


Art.-Nr.: 10.01.42.00034

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Elastodur ED
Malzeme sertliği [Shore A]	85.0 Shore A
Boyut	30.00
Körük Sayısı	1.5
Bağlantı	G1/4-AG
Meme ucu malzemesi	Alüminyum

SAXB 30 ED-85 G1/4-AG

Çeşitli çaplarda mevcut olan körüklü vantuz SAXB, pozitif olarak kalıplanmış bir bağlantı nipel ile birlikte tedarik edilir.

**Tasarım verileri**

Attribute	Value
Yükseklik H	28.00 mm
Dış çap D1	29.9 mm
Dış G1	G1/4"-M
Dış uzunluğu LG1	10.0 mm
Anahtar boyutu SW1	17.0 mm
Yay stroku Z	9.0 mm
Çap Ds	28.9 mm
Çap Dmax(S)	33.0 mm

Tasarım verileri SAXB 30 ED-85 G1/4-AG



Art.-Nr.: 10.01.42.00034

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Elastodur ED
Malzeme sertliđi [Shore A]	85.0 Shore A
Hortum apı (tavsiye edilen) d	4.0 mm
İř parası yarıapı dak (dışbükey)	12.5 mm
Emme kuvveti (-600mbar)	24.00 N
Ağırlık	15.0 g
Yanal kuvvet	24.0 N
Yanal kuvvet yağlı yüzey	20.0 N
Cilt	5.300 cm ³
Boyut	30.00
Körük Sayısı	1.5
Bađlantı	G1/4"-M
Ürün ailesi	SAXB

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.42.00034

WWW.SCHMALZ.COM/10.01.42.00034