

Art.-Nr.: 10.01.42.00035




SAXB 30 ED-85 G3/8-AG

Çeşitli çaplarda mevcut olan körüklü vantuz SAXB, pozitif olarak kalıplanmış bir bağlantı nipelini ile birlikte tedarik edilir.

Teknik veriler

Attribute	Value
Vantuz malzemesi	Elastodur ED
Malzeme sertliği [Shore A]	85.0 Shore A
Boyut	30.00
Körük Sayısı	1.5
Bağlantı	G3/8-AG
Meme ucu malzemesi	Alüminyum



Tasarım verileri SAXB 30 ED-85 G3/8-AG

Tasarım verileri

Attribute	Value
Yükseklik H	28.00 mm
Dış çap D1	29.9 mm
Dış G1	G3/8"-M
Dış uzunluğu LG1	10.0 mm
Anahtar boyutu SW1	17.0 mm
Yay stroku Z	9.0 mm
Çap Ds	28.9 mm
Çap Dmax(S)	33.0 mm

Art.-Nr.: 10.01.42.00035

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Elastodur ED
Malzeme sertliđi [Shore A]	85.0 Shore A
Hortum apı (tavsiye edilen) d	4.0 mm
İř parası yarıapı dak (dışbükey)	12.5 mm
Emme kuvveti (-600mbar)	24.00 N
Ağırlık	16.1 g
Yanal kuvvet	24.0 N
Yanal kuvvet yağlı yüzey	20.0 N
Cilt	5.300 cm ³
Boyut	30.00
Körük Sayısı	1.5
Ürün ailesi	SAXB

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.42.00035

WWW.SCHMALZ.COM/10.01.42.00035