

Art.-Nr.: 10.01.42.00041



SAXB 40 ED-85 G3/8-AG


Çeşitli çaplarda mevcut olan körüklü vantuz SAXB, pozitif olarak kalıplanmış bir bağlantı nipelini ile birlikte tedarik edilir.

Teknik veriler

Attribute	Value
Vantuz malzemesi	Elastodur ED
Malzeme sertliği [Shore A]	85.0 Shore A
Boyut	40.00
Körük Sayısı	1.5
Bağlantı	G3/8-AG
Meme ucu malzemesi	Alüminyum

Tasarım verileri

Attribute	Value
Yükseklik H	28.80 mm
Dış çap D1	33.8 mm
Dış G1	G3/8"-M
Dış uzunluğu LG1	10.0 mm
Anahtar boyutu SW1	17.0 mm
Yay stroku Z	9.8 mm
Çap Ds	39.4 mm
Çap Dmax(S)	44.0 mm



Tasarım verileri SAXB 40 ED-85 G3/8-AG

Art.-Nr.: 10.01.42.00041

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Elastodur ED
Malzeme sertliđi [Shore A]	85.0 Shore A
Hortum apı (tavsiye edilen) d	4.0 mm
İř parası yarıapı dak (dışbükey)	18.0 mm
Emme kuvveti (-600mbar)	42.00 N
Ağırlık	17.7 g
Yanal kuvvet	45.0 N
Yanal kuvvet yağlı yüzey	37.0 N
Cilt	8.700 cm ³
Boyut	40.00
Körük Sayısı	1.5
Ürün ailesi	SAXB

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.42.00041

WWW.SCHMALZ.COM/10.01.42.00041