




SAXB 50 ED-85 G1/4-AG

Çeşitli çaplarda mevcut olan körüklü vantuz SAXB, pozitif olarak kalıplanmış bir bağlantı nipelini ile birlikte tedarik edilir.

Teknik veriler

Attribute	Value
Vantuz malzemesi	Elastodur ED
Malzeme sertliği [Shore A]	85.0 Shore A
Boyut	50.00
Körük Sayısı	1.5
Bağlantı	G1/4-AG
Meme ucu malzemesi	Alüminyum



Tasarım verileri SAXB 50 ED-85 G1/4-AG

Tasarım verileri

Attribute	Value
Yükseklik H	36.90 mm
Dış çap D1	43.2 mm
Dış G1	G1/4"-M
Dış uzunluğu LG1	10.0 mm
Anahtar boyutu SW1	22.0 mm
Yay stroku Z	11.6 mm
Çap Ds	49.6 mm
Çap Dmax(S)	55.0 mm

Art.-Nr.: 10.01.42.00046

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Elastodur ED
Malzeme sertliđi [Shore A]	85.0 Shore A
Hortum apı (tavsiye edilen) d	6.0 mm
İř parası yarıapı dak (dışbükey)	22.0 mm
Emme kuvveti (-600mbar)	58.00 N
Ağırlık	34.6 g
Yanal kuvvet	78.0 N
Yanal kuvvet yağlı yüzey	67.0 N
Cilt	18.900 cm ³
Boyut	50.00
Körük Sayısı	1.5
Ürün ailesi	SAXB

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.42.00046

WWW.SCHMALZ.COM/10.01.42.00046