

Art.-Nr.: 10.01.42.00049




Teknik veriler

Attribute	Value
Vantuz malzemesi	Elastodur ED
Malzeme sertliği [Shore A]	85.0 Shore A
Boyut	100.00
Körük Sayısı	1.5
Bağlantı	G1/4-AG
Meme ucu malzemesi	Alüminyum

SAXB 100 ED-85 G1/4-AG

Çeşitli çaplarda mevcut olan körüklü vantuz SAXB, pozitif olarak kalıplanmış bir bağlantı nipelini ile birlikte tedarik edilir.



Tasarım verileri

Attribute	Value
Yükseklik H	56.60 mm
Dış çap D1	78.4 mm
Dış G1	G1/4"-M
Dış uzunluğu LG1	10.0 mm
Anahtar boyutu SW1	22.0 mm
Yay stroku Z	25.8 mm
Çap Ds	99.6 mm
Çap Dmax(S)	109.0 mm

Tasarım verileri SAXB 100 ED-85 G1/4-AG



Art.-Nr.: 10.01.42.00049

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Elastodur ED
Malzeme sertliđi [Shore A]	85.0 Shore A
Hortum apı (tavsiye edilen) d	6.0 mm
İř parası yarıapı dak (dışbükey)	45.0 mm
Emme kuvveti (-600mbar)	210.00 N
Ağırlık	80.3 g
Yanal kuvvet	264.0 N
Yanal kuvvet yağlı yüzey	243.0 N
Cilt	138.400 cm ³
Boyut	100.00
Körük Sayısı	1.5
Bađlantı	G1/4"-M
Ürün ailesi	SAXB

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.42.00049

WWW.SCHMALZ.COM/10.01.42.00049