


Art.-Nr.: 10.01.42.00050



SAXB 100 ED-85 G1/4-IG

Çeşitli çaplarda mevcut olan körüklü vantuz SAXB, pozitif olarak kalıplanmış bir bağlantı nipelini ile birlikte tedarik edilir.



Tasarım verileri SAXB 100 ED-85 G1/4-IG

Teknik veriler

Attribute	Value
Vantuz malzemesi	Elastodur ED
Malzeme sertliği [Shore A]	85,0 Shore A
Boyut	100,00
Körük Sayısı	1,5
Bağlantı	G1/4-IG
Meme ucu malzemesi	Pirinç

Tasarım verileri

Attribute	Value
Yükseklik H	61,50 mm
Dış çap D1	78,4 mm
Dış G1	G1/4"-F
Dış uzunluğu LG1	15,0 mm
Anahtar boyutu SW1	22,0 mm
Yay stroku Z	25,8 mm
Çap Ds	99,6 mm
Çap Dmax(S)	109,0 mm

Art.-Nr.: 10.01.42.00050

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Elastodur ED
Malzeme sertliđi [Shore A]	85,0 Shore A
Hortum apı (tavsiye edilen) d	6,0 mm
İř parası yarıapı dak (dışbükey)	45,0 mm
Emme kuvveti (-600mbar)	210,00 N
Ağırlık	85,60 g
Yanal kuvvet	264,0 N
Yanal kuvvet yağlı yüzey	243,0 N
Cilt	138,400 cm ³
Boyut	100,00
Körük Sayısı	1,5
Bađlantı	G1/4" -F
Ürün ailesi	SAXB

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.42.00050

WWW.SCHMALZ.COM/10.01.42.00050