




Teknik veriler

Attribute	Value
Vantuz malzemesi	Elastodur ED
Malzeme sertliği [Shore A]	85,0 Shore A
Boyut	120,00
Körük Sayısı	1,5
Bağlantı	G3/8-AG
Meme ucu malzemesi	Alüminyum

SAXB 120 ED-85 G3/8-AG

Çeşitli çaplarda mevcut olan körüklü vantuz SAXB, pozitif olarak kalıplanmış bir bağlantı nipelini ile birlikte tedarik edilir.



Tasarım verileri

Attribute	Value
Yükseklik H	67,80 mm
Dış çap D1	95,0 mm
Dış G1	G3/8"-M
Dış uzunluğu LG1	10,0 mm
Anahtar boyutu SW1	22,0 mm
Yay stroku Z	32,0 mm
Çap Ds	120,6 mm
Çap Dmax(S)	131,0 mm

Tasarım verileri SAXB 120 ED-85 G3/8-AG

Art.-Nr.: 10.01.42.00061

**Teknik veriler**

Attribute	Value
Vantuz malzemesi	Elastodur ED
Malzeme sertliđi [Shore A]	85,0 Shore A
Hortum apı (tavsiye edilen) d	6,0 mm
İř parası yarıapı dak (dışbükey)	67,5 mm
Emme kuvveti (-600mbar)	275,00 N
Ağırlık	124,4 g
Yanal kuvvet	479,0 N
Yanal kuvvet yağlı yüzey	380,0 N
Cilt	251,700 cm ³
Boyut	120,00
Körük Sayısı	1,5
Bađlantı	G3/8"-M
Ürün ailesi	SAXB

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.42.00061

WWW.SCHMALZ.COM/10.01.42.00061