

Körüklü vantuzlar (yuvarlak)

SAXB 120 ED-85 RA




Art.-Nr.: 10.01.42.00063



SAXB 120 ED-85 RA

Çeşitli çaplarda mevcut olan körüklü vantuz SAXB, pozitif olarak kalıplanmış bir bağlantı nipelini ile birlikte tedarik edilir.



Tasarım verileri SAXB 120 ED-85 RA

Teknik veriler

Vantuz malzemesi	Elastodur ED
Malzeme sertliği [Shore A]	85,0 Shore A
Boyut	120,00
Körük Sayısı	1,5
Bağlantı	RA
Meme ucu malzemesi	Alüminyum

Tasarım verileri

Yükseklik H	72,50 mm
Dış çap D1	95,0 mm
Anahtar boyutu SW1	22,0 mm
Yay stroku Z	32,0 mm
Çap Ds	120,6 mm
Uzunluk L4	31,80 mm
Çap Dmax(S)	131,0 mm



WWW.SCHMALZ.COM/10.01.42.00063

Körüklü vantuzlar (yuvarlak)
SAXB 120 ED-85 RA



Art.-Nr.: 10.01.42.00063



Teknik veriler

Vantuz malzemesi	Elastodur ED
Malzeme sertliği [Shore A]	85,0 Shore A
Hortum çapı (tavsiye edilen) d	8,0 mm
İş parçası yarıçapı dak (dışbükey)	67,5 mm
Emme kuvveti (-600mbar)	275,00 N
Ağırlık	126,00 g
Yanal kuvvet	479,0 N
Yanal kuvvet yağlı yüzey	380,0 N
Cilt	251,700 cm ³
Boyut	120,00
Körük Sayısı	1,5
Bağlantı	Dikdörtgen adaptör
Ürün ailesi	SAXB

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



WWW.SCHMALZ.COM/10.01.42.00063