




SAXB 20 ED-85 M16-AG

Çeşitli çaplarda mevcut olan körüklü vantuz SAXB, pozitif olarak kalıplanmış bir bağlantı nipelini ile birlikte tedarik edilir.

Teknik veriler

Attribute	Value
Vantuz malzemesi	Elastodur ED
Malzeme sertliği [Shore A]	85.0 Shore A
Boyut	20.00
Körük Sayısı	1.5
Bağlantı	M16-AG
Meme ucu malzemesi	Alüminyum



Tasarım verileri SAXB 20 ED-85 M16-AG

Tasarım verileri

Attribute	Value
Yükseklik H	25.00 mm
Dış çap D1	20.6 mm
Dış G1	M16-M
Dış uzunluğu LG1	11.0 mm
Anahtar boyutu SW1	17.0 mm
Yay stroku Z	5.8 mm
Çap Ds	20.4 mm
Çap Dmax(S)	23.5 mm

Bellows suction cups (round)

SAXB 20 ED-85 M16-AG



Art.-Nr.: 10.01.42.00078



Teknik veriler

Attribute	Value
Vantuz malzemesi	Elastodur ED
Malzeme sertliđi [Shore A]	85.0 Shore A
Hortum apı (tavsiye edilen) d	4.0 mm
İř parası yarıapı dak (dışbükey)	8.0 mm
Emme kuvveti (-600mbar)	18.00 N
Ağırlık	17.0 g
Yanal kuvvet	13.0 N
Yanal kuvvet yağlı yüzey	9.5 N
Cilt	1.900 cm ³
Boyut	20.00
Körük Sayısı	1.5
Bađlantı	M16-M
Ürün ailesi	SAXB

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.42.00078



WWW.SCHMALZ.COM/10.01.42.00078