

Art.-Nr.: 10.01.42.00085



SAXB 30 ED-85 M16-AG


Çeşitli çaplarda mevcut olan körüklü vantuz SAXB, pozitif olarak kalıplanmış bir bağlantı nipelini ile birlikte tedarik edilir.

Teknik veriler

Attribute	Value
Vantuz malzemesi	Elastodur ED
Malzeme sertliği [Shore A]	85,0 Shore A
Boyut	30,00
Körük Sayısı	1,5
Bağlantı	M16-AG
Meme ucu malzemesi	Alüminyum

Tasarım verileri

Attribute	Value
Yükseklik H	28,00 mm
Dış çap D1	29,9 mm
Dış G1	M16-M
Dış uzunluğu LG1	11,0 mm
Anahtar boyutu SW1	17,0 mm
Yay stroku Z	9,0 mm
Çap Ds	28,9 mm
Çap Dmax(S)	33,0 mm



Tasarım verileri SAXB 30 ED-85 M16-AG

Bellows suction cups (round)

SAXB 30 ED-85 M16-AG



Art.-Nr.: 10.01.42.00085



Teknik veriler

Attribute	Value
Vantuz malzemesi	Elastodur ED
Malzeme sertliđi [Shore A]	85,0 Shore A
Hortum apı (tavsiye edilen) d	4,0 mm
İř parası yarıapı dak (dışbükey)	12,5 mm
Emme kuvveti (-600mbar)	24,00 N
Ağırlık	18,10 g
Yanal kuvvet	24,0 N
Yanal kuvvet yağlı yüzey	20,0 N
Cilt	5,300 cm ³
Boyut	30,00
Körük Sayısı	1,5
Bađlantı	M16-M
Ürün ailesi	SAXB

Note: Suction force: The suction force values are theoretical values at -0.6 bar vacuum and a dry, smooth and even workpiece surface – they are specified without safety factors. Hose inner diameter: The recommended hose diameter refers to a hose length of approx. 2 m



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.42.00085



WWW.SCHMALZ.COM/10.01.42.00085