

Art.-Nr.: 10.01.43.00001



FXCB-SW110 300 3R18 O20 VSi NO


The large-area gripping system FXCB is delivered as a ready-to-connect product.

Technical data

Attribute	Value
Nozzle diameter	1.1 mm
Construction vacuum switch	PNP switching
Weight	2.000 kg
Design vacuum generator	Ejector module SEP
Additional function area gripper	1x control valve vacuum / blow-off
Length L	300.00 mm
Width B	130.00 mm
Height H	131.40 mm
Arrangement	3R18
Control valve	Normally open

Design data

Attribute	Value
Length L1	331.00 mm
Length L2	99.00 mm
Length L	300.00 mm
Width B1	159.00 mm
Width B	130.00 mm
Height H1	137.40 mm
Height H2	20.00 mm
Height H	131.40 mm
Nominal diameter dn	10.00 mm
Length L3	102.00 mm



Design data FXCB-SW110 300 3R18 O20 VSi NO

Art.-Nr.: 10.01.43.00001

**Technical data**

Attribute	Value
Weight	2.000 kg
Material type	Foam O, Height 20 mm
Number of suction cells	45
Suction rate (max.)	354.0 l/min

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.43.00001**Ordering Data Accessories 10.01.43.00001**

Typ		Item number
Connection cable	ASK B-M12-8 280 WB-M8-8 UR	21.04.05.00350
Distributor	ASV ECBPi WS-M8-3 WS-M8-8	21.04.05.00361
Distributor	ASV ECBPi WS-M8-4 WS-M8-8	21.04.05.00362
Connection cable	ASK B-M12-8 5000 K-8P	21.04.05.00079
Vacuum hose (meter)	VSL 10-7 PU MI-TR	10.07.09.00084

**Ordering Data Spare Parts 10.01.43.00001**

Typ		Item number
Masking foil (glued)	MASK-FOL SW110 294 3R18 FLGR	10.01.11.03375
Sealing plate (FX/FM)	DI-PL 300x130 3R18 LL-20x7 O20 KE	10.01.11.03658
Silencer (cube-shaped)	SD 97x34x20 FXCB	10.01.43.00005
Vacuum/pressure switch	VSi V D M8-4	10.06.02.00577
Housing (complex shape)	GEH 314.6x144.2x91.7 FXCB-FMCB	10.01.43.00021

