

Art.-Nr.: 10.01.43.00070




Technical data

Attribute	Value
Nozzle diameter	1.5 mm
Construction vacuum switch	PNP switching
Weight	2.200 kg
Design vacuum generator	Ejector module SEP
Additional function area gripper	1x control valve vacuum / blow-off
Length L	297.00 mm
Width B	123.20 mm
Height H	158.00 mm
Arrangement	3R54
Control valve	Normally open

FXCB-SW150 297 3R54 SPB2 40 P VSi NO

The large-area gripping system FXCB is delivered as a ready-to-connect product.



Design data

Attribute	Value
Length L1	331.00 mm
Length L2	114.40 mm
Length L	297.00 mm
Width B1	159.00 mm
Width B	123.20 mm
Height H1	164.00 mm
Height H2	47.00 mm
Height H	158.00 mm
Nominal diameter dn	10.00 mm
Length L3	102.00 mm

Design data FXCB-SW150 297 3R54 SPB2 40 P VSi NO



Art.-Nr.: 10.01.43.00070

**Technical data**

Attribute	Value
Weight	2.200 kg
Number of suction cells	15
Suction rate (max.)	354.0 l/min
Product family	FXCB
Lift capacity (vertical)	80.0 N
Lift capacity (horizontal)	350.0 N

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.43.00070**Ordering Data Accessories 10.01.43.00070**

Typ		Item number
Connection cable	ASK B-M12-8 280 WB-M8-8 UR	21.04.05.00350
Distributor	ASV ECBPi WS-M8-3 WS-M8-8	21.04.05.00361
Distributor	ASV ECBPi WS-M8-4 WS-M8-8	21.04.05.00362
Connection cable	ASK B-M12-8 5000 K-8P	21.04.05.00079
Vacuum hose (meter)	VSL 10-7 PU MI-TR	10.07.09.00084

**Ordering Data Spare Parts 10.01.43.00070**

Typ		Item number
Bellows suction cup (round)	SPB2 40 SI-55 P	10.01.06.03126
Flow resistance	SW 150 P 7.3	10.05.04.00093
Housing (complex shape)	GEH 314.6x144.2x91.7 FXCB-FMCB	10.01.43.00021
Vacuum/pressure switch	VSi V D M8-4	10.06.02.00577
Silencer (cube-shaped)	SD 97x34x20 FXCB	10.01.43.00005

