

Art.-Nr.: 10.01.43.00133



Technical data

Attribute	Value
Construction vacuum switch	NPN switching
Type	TM5, TM12, TM14
Control valve for	Normally open OMRON

ROB-SET FXCB OMRON SPB2

The robot set FXCB is delivered unassembled. The delivery consists of:


- Area gripping system FXCB
- Flange module MOD-FLAN (optional)
- Connection cable ASK-B
- USB stick with software (optional)

Available spare parts: flange module MOD-FLAN (optional), connection cable ASK-B, front foil MASK-FOL, solenoid valve EMV, sealing plate DI-PL, silencer SD

Available accessories: vacuum / compressed air hose VSL



Art.-Nr.: 10.01.43.00133

**Design data**

Attribute	Value
Length L1	331.00 mm
Length L2	114.40 mm
Length L	297.00 mm
Width B1	159.00 mm
Width B2	45.00 mm
Width B	123.20 mm
Height H1	195.50 mm
Height H2	47.00 mm
Height H	190.50 mm
Nominal diameter dn	10.00 mm

Design data ROB-SET FXCB OMRON SPB2

**Technical data**

Attribute	Value
Weight	2.600 kg
Number of suction cells	15
Suction rate (max.)	525.9 l/min
Product family	ROB-SET-FXCB
Lift capacity (vertical)	80.0 N
Lift capacity (horizontal)	350.0 N
for	OMRON

The technical properties of the robot types may vary by region. The stated compatibility of the set is based on standard European models.

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.01.43.00133**Ordering Data Spare Parts 10.01.43.00133**

Typ		Item number
Solenoid valve	EMVP 2.35 24V-DC 2x3/2 CAR NO/NC	10.01.11.03420
Silencer (cube-shaped)	SD 97x34x20 FXCB	10.01.43.00005
Vacuum/pressure switch	VSi V D M8-4	10.06.02.00577
Bellows suction cup (round)	SPB2 40 SI-55 P	10.01.06.03126

WWW.SCHMALZ.COM/10.01.43.00133