

Art.-Nr.: 10.01.55.00022


**Technical data**

Max. vacuum	-980 mbar
Voltage at 50 Hz	D230 V / Y400 V ± 10 %
Suction rate (max.)	63.000 m ³ /h
Additional function ejector	Vacuum switch digital
Reservoir volume	100.0 l
Design vacuum generator	Oil-lubricated pump EVE-OG
Width B	623.00 mm
Height H	862.00 mm
Functionality of the ejector with	electronic air-saving function Filter
Shape	Plus

VH-OG Plus 63 100

The vacuum unit VH-OG Plus is delivered as a ready-to-connect product.

- Available spare parts: vacuum switch, oil, wear parts kit for vacuum pump, vacuum pump, filter, non-return valve
- Available accessories: vacuum hose, roller set

**Design data**

Length L	823.00 mm
Width B	623.00 mm
Height H	862.00 mm
Outside diameter D with	38.00 mm Filter

Design data VH-OG Plus 63 100



Art.-Nr.: 10.01.55.00022

**Technical data**

Max. vacuum	-980 mbar
Voltage at 50 Hz	D230 V / Y400 V ± 10 %
Suction rate (max.)	63.000 m ³ /h
Additional function ejector	Vacuum switch digital
Reservoir volume	100.0 l
Functionality of the ejector	electronic air-saving function

**Ordering Data Accessories 10.01.55.00022**

Typ		Item number
Accessories	ZUB EVE-OG Ölablass-Kit	22.09.03.00038
Vacuum hose (meter)	VSL 41-32 PVC-DS KL-TR	10.07.09.00008
Accessories	ZUB VH 4CAS	10.01.27.02333

**Ordering Data Spare Parts 10.01.55.00022**

Typ		Item number
Vacuum pump	EVE-OG 63 AC3	10.03.02.00027
Oil	OEL EVE-OG 1L ANDEROL 555	27.02.01.00055
Vacuum/pressure switch cube shape	VS-VP10-W-D M8-4 UH IOL	10.06.02.00883
Dust filter	STF G1-1/4-IG N	10.07.01.00008
Filter insert (round)	FILT-EINS 3 98x70 PAP STF-1-1/4-IGN	10.07.01.00018

**Ordering Data Wear Parts 10.01.55.00022**

Typ		Item number
Set of parts subject to wear pump	VST EVE-OG-63-100	10.03.02.00055

