




SBP HV 2 04 7 KU

The basic ejectors SBP-HV/HF is delivered as a ready to connect component.

Available accessories: silencer

Technical data

Attribute	Value
Nozzle diameter	0.4 mm
Degree of evacuation	79.0 %
Material	Plastics
Air consumption suction	6.5 l/min
Suction rate (max.)	13.2 l/min
Size	7.00
Number of stages	2
Shape	High vacuum



Design data SBP HV 2 04 7 KU

Design data

Attribute	Value
Length L1	47.50 mm
Length L2	10.00 mm
Length L	36.50 mm
Width B	19.00 mm
Height H2	5.00 mm
Height H	25.00 mm
Outside diameter D	6.00 mm
d2	4.2 mm
Thread G1	G1/8"-F
Thread G2	G1/8"-F


Art.-Nr.: 10.02.01.01958

**Technical data**


Attribute	Value
Nozzle diameter	0.4 mm
Recommended hose internal diameter compressed air	2.0 mm
Recommended hose internal diameter vacuum	4.0 mm
Degree of evacuation	79.0 %
Sound pressure level suction	57.0 dB(A)
Sound pressure level free	65.0 dB(A)
Weight	21.5 g
Air consumption suction	0.229 cfm
Suction rate (max.)	0.466 cfm
Number of stages	2
Pressure range (operating pressure) [bar]	29.0 ... 87.0
Operating temperature	0 ... 60 °C
Product family	SBP-HV-HF-KU




Art.-Nr.: 10.02.01.01958

**Performance data**

Achievable vacuum at various operating pressures



Suction rate at various degrees of evacuation [l/min]



Evacuation time for various vacuum ranges [s/l]

**Achievable vacuum at various operating pressures**

	1	2	3	4	5	6
SBP-HV 2 04 7 KU	-	380	640	790	860	840
SBP-HV...07 13 KU	-	365	650	840	860	860
SBP-HV...16 22 KU	-	375	715	900	890	890



Art.-Nr.: 10.02.01.01958

**Suction rate at various degrees of evacuation [l/min]**

	0	100	200	300	400	500	600	700
SBP-HV 2 04 7 KU	13.2	9.5	4.4	3.4	2.9	2.3	1.7	1.2
SBP-HV 2 07 13 KU	42.5	33.6	25.0	13.7	8.7	7.3	4.6	2.7
SBP-HV 3 07 13 KU	76.8	39	26.9	16	9.2	7.6	5.1	3.1
SBP-HV 2 16 22 KU	159	137.3	112.6	81.2	50.5	25	17.7	11.1
SBP-HV 3 16 22 KU	308.8	160	112.6	81.2	50.5	25	17.7	11.1

**Evacuation time for various vacuum ranges [s/l]**

	0	100	200	300	400	500	600	700	800
SBP-HV 2 04 7 KU	-	0.53	1.34	2.79	4.71	7.16	10.68	17.73	25
SBP-HV 2 07 13 KU	-	0.09	0.26	0.56	1.22	2.08	3.21	5.09	9.71
SBP-HV 3 07 13 KU	-	0.11	0.28	0.53	1.11	1.94	3.01	4.71	8.47
SBP-HV 2 16 22 KU	-	0.06	0.09	0.14	0.23	0.4	0.61	0.94	1.49
SBP-HV 3 16 22 KU	-	0.04	0.08	0.12	0.21	0.36	0.58	0.90	1.46

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.02.01.01958**Ordering Data Spare Parts 10.02.01.01958**

Typ		Item number
Schmalz Fixation Element	SFE 7 POM	10.02.01.01808
Ejector module	SEP HV 2 04 7	10.02.01.01393
Schmalz Holder Cap	SHC 2 7	10.02.01.01510

WWW.SCHMALZ.COM/10.02.01.01958