




EIP 10 S04 EA

The basic ejector EIP is delivered as a ready-to-connect product.



Design data EIP 10 S04 EA

Technical data

Connection	Hose D6(1)-D6(2)
Nozzle size	10

Design data

Length L2	25.50 mm
Length L	50.50 mm
Outside diameter D	16.20 mm
Internal diameter d1	6.0 mm
Internal diameter d	6.00 mm
Thread G1	G1/8"-M
Thread length LG1	7.0 mm
Key width SW1	17.0 mm

Inline ejector

EIP 10 S04 EA



Art.-Nr.: 10.02.01.02141



Technical data

Nozzle size	1.0 mm
Degree of evacuation	89.0 %
Weight	42.00 g
Suction rate (max.)	1.230 m ³ /h
Optimal operating pressure	4.00 bar
Connection	Hose D6(1)-D6(2)



WWW.SCHMALZ.COM/10.02.01.02141