

Inline ejector
EIP 05 S04



Art.-Nr.: 10.02.01.02142




EIP 05 S04

The basic ejector EIP is delivered as a ready-to-connect product.

Technical data

Connection	Hose D6(1)-D6(2)
Nozzle size	05



Design data EIP 05 S04

Design data

Length L2	25.50 mm
Length L	40.50 mm
Outside diameter D	16.20 mm
Internal diameter d	6.00 mm
Thread G1	G1/8"-M
Thread length LG1	7.0 mm
Key width SW1	17.0 mm



WWW.SCHMALZ.COM/10.02.01.02142

Art.-Nr.: 10.02.01.02142



Technical data

Nozzle size	0.5 mm
Degree of evacuation	89.0 %
Weight	34.50 g
Suction rate (max.)	0.420 m ³ /h
Optimal operating pressure	4.00 bar
Connection	Hose D6(1)-D6(2)

