

Inline ejector  
**EIP 07 S04**



Art.-Nr.: 10.02.01.02143




**Technical data**

Connection	Hose D6(1)-D6(2)
Nozzle size	07

EIP 07 S04

The basic ejector EIP is delivered as a ready-to-connect product.



**Design data**

Length L2	25.50 mm
Length L	40.50 mm
Outside diameter D	16.20 mm
Internal diameter d	6.00 mm
Thread G1	G1/8"-M
Thread length LG1	7.0 mm
Key width SW1	17.0 mm

Design data EIP 07 S04



[WWW.SCHMALZ.COM/10.02.01.02143](http://WWW.SCHMALZ.COM/10.02.01.02143)

Inline ejector

## EIP 07 S04



Art.-Nr.: 10.02.01.02143



### Technical data

Nozzle size	0.7 mm
Degree of evacuation	89.0 %
Weight	34.50 g
Suction rate (max.)	0.840 m <sup>3</sup> /h
Optimal operating pressure	4.00 bar
Connection	Hose D6(1)-D6(2)



[WWW.SCHMALZ.COM/10.02.01.02143](http://WWW.SCHMALZ.COM/10.02.01.02143)