

Compact ejector
SCP 15 NO AS VD



Art.-Nr.: 10.02.02.00617



Technical data


Nozzle diameter	1.5 mm
Air consumption suction	117.0 l/min
Suction rate (max.)	65.0 l/min
Pressure range (operating pressure) [bar]	bar
Shape compact ejectors	With blow-off system
Control valve	Normally open
Functionality	digital vacuum switch

SCP 15 NO AS VD

Compact ejector SCP is delivered as a ready to connect product (without connection cable).

Available spare parts: silencer box, filter element

Available accessories: connection cable, connection plug



Design data

Length L2	7.00 mm
Length L	71.50 mm
Width B	20.20 mm
Height H1	162.00 mm
Height H2	36.50 mm
Height H	42.20 mm
Internal diameter d	4.50 mm
Thread G1	G1/8"-F
Thread G2	G1/8"-F
Height H3	15.00 mm
Hole spacing Y1	12.0 mm
Hole spacing X1	41.5 mm
Hole spacing X2	58.5 mm

Design data SCP 15 NO AS VD



WWW.SCHMALZ.COM/10.02.02.00617

Compact ejector

SCP 15 NO AS VD



Art.-Nr.: 10.02.02.00617



Technical data

Nozzle diameter	1.5 mm
Degree of evacuation	85.0 %
Suction rate (max.)	2.295 cfm
Product family	SCP
Control valve	Normally open

Note: The supply voltage for vacuum switches and solenoid valves is 24V DC Air consumption: At optimal operating pressure Hose diameter: For max. length 2 m



Ordering Data Accessories 10.02.02.00617

Typ		Item number
Connection cable	ASK B-MIC10 3000 K-2P	21.04.06.00086
Connection cable	ASK B-M8-4 5000 K-4P	10.06.02.00031
Connection cable	ASK WB-M8-4 5000 K-4P	10.06.02.00032



Ordering Data Spare Parts 10.02.02.00617

Typ		Item number
Filter insert (round)	FILT-EINS 13x33 PE-POR SCP	10.02.02.00655
Silencer (cube-shaped)	SD 28x19x31.5 SCP10/15	10.02.02.00653



WWW.SCHMALZ.COM/10.02.02.00617