



SCP 15 NC AS RD


Kompakt ejektör SCP bağlanmaya hazır bir ürün olarak teslim edilir (bağlantı kablosu olmadan).

Mevcut yedek parçalar: susturucu kutusu, filtre elemanı

Mevcut aksesuarlar: bağlantı kablosu, bağlantı fişi

Teknik veriler

Attribute	Value
Nozul çapı	1,5 mm
Hava tüketimi emiş	117,0 l/min
Vakum debisi (maks.)	65,0 l/min
Basınç aralığı (çalışma basıncı) [bar]	bar
Şekil kompakt ejektörler	Üfleme sistemi ile
Kontrol Valfi	Normalde kapalı
Çalışma modu	Dijital hava tasarruf fonksiyonu



Tasarım verileri SCP 15 NC AS RD

Tasarım verileri

Attribute	Value
Uzunluk L2	7,00 mm
Uzunluk L	71,50 mm
Genişlik B	20,20 mm
Yükseklik H1	205,00 mm
Yükseklik H2	36,50 mm
Yükseklik H	42,20 mm
İç çap d	4,50 mm
Diş G1	G1/8"-F
Diş G2	G1/8"-F
Yükseklik H3	15,00 mm
Delik aralığı Y1	12,0 mm
Delik aralığı X1	41,5 mm
Delik aralığı X2	58,5 mm

Art.-Nr.: 10.02.02.00783

**Teknik veriler**

Attribute	Value
Nozul çapı	1,5 mm
Tahliye derecesi	85,0 %
Vakum debisi (maks.)	2,295 cfm
Ürün ailesi	SCP
Kontrol Valfi	Normalde kapalı

Note: The supply voltage for vacuum switches and solenoid valves is 24V DC Air consumption: At optimal operating pressure Hose diameter: For max. length 2 m

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.02.02.00783

**Sipariş Verisi Yedek Parça 10.02.02.00783**

Typ		Ürün numarası
Filtre eki (yuvarlak)	FILT-EINS 13x33 PE-POR SCP	10.02.02.00655
Susturucu (küp şekli)	SD 28x19x31.5 SCP10/15	10.02.02.00653

WWW.SCHMALZ.COM/10.02.02.00783