


Art.-Nr.: 10.02.02.00919



GP 4 SMP 15..20/SCP 20

## Technical data

| Attribute                                 | Value     |
|-------------------------------------------|-----------|
| Number of connections                     | 4         |
| Pressure range (operating pressure) [bar] | bar       |
| Length L                                  | 124.00 mm |
| Width B                                   | 38.00 mm  |
| Height H                                  | 49.50 mm  |
| Internal diameter d                       | 7.00 mm   |



Design data GP 4 SMP 15..20/SCP 20

## Design data

| Attribute           | Value     |
|---------------------|-----------|
| Length L            | 124.00 mm |
| Width B2            | 7.00 mm   |
| Width B             | 38.00 mm  |
| Height H2           | 8.00 mm   |
| Height H            | 49.50 mm  |
| Internal diameter d | 7.00 mm   |
| Thread G1           | G1/2"-F   |
| Width B3            | 16.00 mm  |
| Hole spacing Y2     | 34.0 mm   |
| Hole spacing X1     | 108.0 mm  |



## Technical data

| Attribute | Value   |
|-----------|---------|
| Weight    | 595.0 g |



Compressed-air connection plate

## GP 4 SMP 15..20/SCP 20



Art.-Nr.: 10.02.02.00919



### Further documentation

CAD data and other documents relating to the article can be found at: [www.schmalz.com/10.02.02.00919](http://www.schmalz.com/10.02.02.00919)



### Ordering Data Spare Parts 10.02.02.00919

| Typ                    |                                   | Item number    |
|------------------------|-----------------------------------|----------------|
| Ejector blanking plate | EJEK-PL SMP(i)15..30/SCP(i)20..30 | 10.02.02.00728 |
| O-ring                 | O-RING 14x1.5 NBR-70              | 10.07.08.00150 |



[WWW.SCHMALZ.COM/10.02.02.00919](http://WWW.SCHMALZ.COM/10.02.02.00919)