

Art.-Nr.: 10.02.02.04374



SCPSb 2-09 S04 NC

Compact ejector SCPSb is delivered as a ready-to-connect product (without connection cable).


Available accessories: connection cable, top-hat rail clamp, vacuum filter, compressed air connection plate, mounting set, exhaust air set

Technical data

Max. vacuum	-850 mbar
Air consumption suction	40.5 l/min
Suction rate (max.)	49.5 l/min
Connection	Hose D6(1)-D6(2)
Nozzle size	2-09
Control valve	Normally closed

Design data

Length L1	109.50 mm
Width B1	18.60 mm
Height H1	97.00 mm
Internal diameter d1	6.0 mm
d2	6.0 mm
Internal diameter d	4.40 mm
Hole size d3	2.6 mm
Length L3	22.00 mm
Hole spacing Y1	12.0 mm
Hole spacing Y2	12.0 mm
Hole spacing X1	36.9 mm
Hole spacing X2	16.0 mm



Design data SCPSb 2-09 S04 NC



Art.-Nr.: 10.02.02.04374

**Technical data**

Protection type IP	IP 40 (with plug)
Degree of evacuation	85.0 %
Weight	0.165 kg
Max. air consumption blow-off	120.0 l/min
Air consumption blow-off	7.200 m ³ /h
Suction rate (max.)	3.050 m ³ /h
Optimal operating pressure	4.50 bar
Pressure range (operating pressure) [bar]	3.0 ... 6.0 bar
Product family	SCPSb
Nozzle size	2-09
Control valve	Normally closed




Compact ejector SCPSb 2-09 S04 NC




Art.-Nr.: 10.02.02.04374




Performance data



Achievable vacuum at various operating pressures



Evacuation time for various vacuum ranges [s/l]



Suction rate at various degrees of evacuation [l/min]



Achievable vacuum at various operating pressures

	2	3	4	5	6
SCPSb 10	470	700	850	830	815
SCPSb 2-09	420	640	820	875	850



WWW.SCHMALZ.COM/10.02.02.04374

Art.-Nr.: 10.02.02.04374

**Evacuation time for various vacuum ranges [s/l]**

	0	100	200	300	400	500	600	700	800
SCPSb 10	0.05	0.15	0.3	0.5	0.8	1.2	1.75	2.8	5.5
SCPSb 2-09	0.0	0.0	0.00	0.2	0.45	0.85	1.45	2.5	5.0

**Suction rate at various degrees of evacuation [l/min]**

	0	100	200	300	400	500	600	700	800
SCPSb 10	36.1	29.5	25.7	20.8	16.9	13	8.1	3.4	0.5
SCPSb 2-09	49.6	42.1	34.4	24.7	17	11.4	7.2	3.3	0.5

**Ordering Data Accessories 10.02.02.04374**

Typ		Item number
Exhaust air set	ABL-SET SCPS zweistufig	10.02.02.04667
Connection cable	ASK B-MIC10 3000 K-2P	21.04.06.00086
Top-hat rail clamp comp.	HUT-SN-KL 75x18x9 SCPS	10.02.02.04149
Mounting set	SET SCPS	10.02.02.04343
Conversion kit	UMR-SET SCPSb	10.02.02.04848
Vacuum filter (inline)	VFI CN6/4 50	10.07.01.00241
Vacuum filter (inline)	VFI CN8/6 50	10.07.01.00245

