

Art.-Nr.: 10.02.02.04824


**Technical data**

Max. vacuum	-850 mbar
Air consumption suction	22.0 l/min
Suction rate (max.)	16.0 l/min
Connection	Hose D6(1)-D6(2)
Nozzle size	07
Control valve	Normally open
Functionality of the ejector	digital vacuum switch

SCPSb 07 S04 NO VD

Compact ejector SCPSb is delivered as a ready-to-connect product (without connection cable).

Available accessories: connection cable, top-hat rail clamp, vacuum filter, compressed air connection plate, mounting set, exhaust air set



Design data SCPSb 07 S04 NO VD

**Design data**

Length L1	102.50 mm
Width B1	18.60 mm
Height H1	146.00 mm
Internal diameter d1	6.0 mm
d2	6.0 mm
Internal diameter d	4.40 mm
Hole size d3	2.6 mm
Length L3	22.00 mm
Hole spacing Y1	12.0 mm
Hole spacing Y2	12.0 mm
Hole spacing X1	36.9 mm
Hole spacing X2	16.0 mm



Art.-Nr.: 10.02.02.04824



## Technical data


Protection type IP	IP 40 (with plug)
Degree of evacuation	85.0 %
Weight	0.165 kg
Max. air consumption blow-off	120.0 l/min
Air consumption blow-off	7.200 m <sup>3</sup> /h
Suction rate (max.)	0.980 m <sup>3</sup> /h
Optimal operating pressure	4.50 bar
Pressure range (operating pressure) [bar]	3.0 ... 6.0 bar
Product family	SCPSb
Nozzle size	07
Control valve	Normally open
Functionality of the ejector	digital vacuum switch




Art.-Nr.: 10.02.02.04824




## Performance data



Achievable vacuum at various operating pressures



Evacuation time for various vacuum ranges [s/l]



Suction rate at various degrees of evacuation [l/min]



## Achievable vacuum at various operating pressures

	2	3	4	5	6
SCPSb 07	480.00	700.00	860.00	850.00	830.00
SCPSb 2-07	345.00	560.00	790.00	890.00	880.00



Art.-Nr.: 10.02.02.04824

**Evacuation time for various vacuum ranges [s/l]**

	0	100	200	300	400	500	600	700	800
SCPSb 07	0.15	0.30	0.65	1.10	1.75	2.75	4.00	6.15	10.50
SCPSb 2-07	0.00	0.15	0.40	0.65	1.00	1.5	2.8	4.2	7

**Suction rate at various degrees of evacuation [l/min]**

	0	100	200	300	400	500	600	700	800
SCPSb 07	16.00	12.30	10.50	8.00	6.00	3.80	1.90	1.00	0.30
SCPSb 2-07	37.20	28.10	19.90	12.50	7.50	3.90	2.00	1.00	0.30

**Ordering Data Accessories 10.02.02.04824**

Typ		Item number
Exhaust air set	ABL-SET SCPS einstufig	10.02.02.04216
Connection cable	ASK B-MIC10 3000 K-2P	21.04.06.00086
Connection cable	ASK B-M8-4 5000 K-4P	10.06.02.00031
Top-hat rail clamp comp.	HUT-SN-KL 75x18x9 SCPS	10.02.02.04149
Mounting set	SET SCPS	10.02.02.04343
Vacuum cup filter	VFT G1/8-IG 80	10.07.01.00116
Vacuum filter (inline)	VFI CN6/4 50	10.07.01.00241
Vacuum filter (inline)	VFI 6/4 50	10.07.01.00328
Vacuum hose (meter)	VSL 6-4 PU MI-TR	10.07.09.00002

