

Art.-Nr.: 10.02.02.05737



SCPMb 10 S04 NC AAL


Compact ejector SCPM is delivered as a ready-to-connect product (without connection cable).

Available spare parts: silencer, filter element

Available accessories: connection cable, connection plug

Technical data

Attribute	Value
Protection type IP	IP 40 (with plug)
Max. vacuum	870 mbar
Sound pressure level free	71.0 dB(A)
Air consumption suction	45.0 l/min
Suction rate (max.)	28.0 l/min
Connection	Hose D6(1)-D6(2)
Pressure range (operating pressure) [bar]	3.5 ... 6.0 bar
Control valve	Normally closed



Design data SCPMb 10 S04 NC AAL


Design data

Attribute	Value
Length L1	98.30 mm
Length L	76.50 mm
Width B1	12.50 mm
Width B	12.00 mm
Height H1	64.20 mm
Height H2	24.95 mm
Height H	41.50 mm
Outside diameter D	9.00 mm
Internal diameter d1	6.2 mm
d2	6.2 mm

Art.-Nr.: 10.02.02.05737

**Technical data**

Attribute	Value
Control valve	NC
Recommended hose internal diameter compressed air	4.0 mm
Recommended hose internal diameter vacuum	4.0 mm
Degree of evacuation	87.0 %
Max. vacuum	870 mbar
Weight	74.0 g
Max. air consumption blow-off	10.0 l/min
Air consumption suction	45.0 l/min
Suction rate (max.)	28.0 l/min
Optimal operating pressure	4.50 bar
Pressure range (operating pressure) [bar]	3.5 ... 6.0 bar
Operating temperature	0 ... 50 °C
Product family	SCPMb
Configurator code	AAL

**Performance data**

Achievable vacuum at various operating pressures

**Achievable vacuum at various operating pressures**

Typ	2	2.5	3.0	3.5	4	4.5	5	5.5	6
SCPM 03/05/07	416	512	711	866	880	875	860	850	845
SCPM 10	350	416	512	725	866	880	870	860	850
SCPM 12	330	460	610	740	850	922	930	927	925



Art.-Nr.: 10.02.02.05737

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.02.02.05737**Ordering Data Accessories 10.02.02.05737**

Typ		Item number
Connection cable	ASK B-MIC10 3000 K-2P	21.04.06.00086
Silencer (round)	SD 10.5x31.7 SCPM	10.02.02.05807
Exhaust air set	ABL-SET SCPMi/c/b	10.02.02.06080
Mounting set	SET SCPM MOUNT1	10.02.02.05805
Mounting bracket	BEF-WIN 15x50x36.1 1.5 SCPM	10.02.02.05824
Plug union, straight	STV-GE M5-AG 4	10.08.02.00468
Plug union, straight	STV-GE M7-AG 6	10.08.02.00469
Thread adapter (inst)	ADP-G M7-IG 10.8x7.9 SCPMi/c/b	10.02.02.05522
Thread adapter (inst)	ADP-G M5-IG 10.5x8.6 SCPMi/c/b	10.02.02.05643

**Ordering Data Spare Parts 10.02.02.05737**

Typ		Item number
Silencer insert (round)	SD-EINS 6.4x21.8 SCPMi/c/b	10.02.02.05403

