



SCPMt 10 6/4 NO E1T

Technical data

Attribute	Value
Electrical connection	Flat pin
Protection type IP	IP 54
Max. vacuum	870 mbar
Air consumption suction	58.0 l/min
Suction rate (max.)	28.0 l/min
Connection	6/4
Control valve	Normally open

Design data SCPMt 10 6/4 NO E1T

Design data

Attribute	Value
-----------	-------



Technical data

Attribute	Value
Air consumption suction	58.0 l/min
Suction rate (max.)	28.0 l/min



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.02.02.06945

