



Technical data


Nozzle diameter	1.6 mm
Shape compact ejectors	HD
Electrical connection	Male connect M12, 5 pol
Protection type IP	IP 65 (with plug)
Max. vacuum	-910 mbar
Sound pressure level free	75.0 dB(A)
Air consumption suction	105.6 l/min
Suction rate (max.)	53.2 l/min
Connection	G1/8" (1)-G1/8" (2)
Pressure range (operating pressure) [bar]	3.0 ... 6.0 bar
Control valve	Normally closed
Functionality of the ejector	Digital air-saving function

SCPSc-UHV-HD 16 G02 NC PNP

Compact ejector SCPScb- / SCPSc- / SCPSc- / SCPSci-UHV-HD is delivered as a ready-to-connect product (without connection cable).

Available accessories: connection cable, distributor, top-hat rail clamp, filter, compressed air connection plate, mounting set

Art.-Nr.: 10.02.02.07427

**Design data**

Length L1	148.40 mm
Length L2	91.50 mm
Length L	135.00 mm
Width B1	18.60 mm
Width B	18.00 mm
Height H2	40.80 mm
Height H	99.00 mm
Outside diameter D2	9.0 mm
Outside diameter D	16.50 mm
Internal diameter d	4.40 mm
Thread G1	G1/8"-F
Thread G2	G1/8"-F
Hole size d3	2.6 mm
Length L3	22.00 mm
Length L4	29.50 mm
Height H3	47.50 mm
Height H4	16.50 mm
Hole spacing Y1	12.0 mm
Hole spacing Y2	12.0 mm
Hole spacing X1	36.9 mm

Design data SCPSc-UHV-HD 16 G02 NC PNP

**Technical data**




Degree of evacuation	91.0 %
Sound pressure level suction	77.0 dB(A)
Sound pressure level free	75.0 dB(A)
Weight	0.210 kg
Max. air consumption blow-off	120.0 l/min
Air consumption blow-off	4.237 cfm
Air consumption suction	3.729 cfm
Suction rate (max.)	1.878 cfm
Pressure range (operating pressure) [bar]	3.0 ... 6.0 bar
Operating temperature	0 ... 50 °C
Pressure range (operating pressure) [psi]	43.5 ... 87.0
Max. vacuum	-26.872 inHg
Product family	SCPSc-UHV-HD
Nozzle size	16
Connection	G02
Electrical connection	M12-5
Control valve	Normally closed



Art.-Nr.: 10.02.02.07427



Performance data



Art.-Nr.: 10.02.02.07427

	0	50	100	150	200	250	300	350	400	450	500	550	600	650	700	750	800	850	900
SCPS _b -/ SCPS-/ SCPS _c -/ SCPSi- UHV-HD 07	0.00	0.08	0.25	0.41	0.60	0.81	1.00	1.31	1.62	2.00	2.43	2.92	3.47	4.10	4.85	5.88	7.75	11.39	18.19
SCPS _b -/ SCPS-/ SCPS _c -/ SCPSi- UHV-HD 11	0.00	0.08	0.18	0.26	0.35	0.44	0.55	0.67	0.81	0.97	1.15	1.35	1.59	1.87	2.22	2.64	3.36	4.58	6.52
SCPS _b -/ SCPS-/ SCPS _c -/ SCPSi- UHV-HD 16	0.00	0.07	0.11	0.15	0.20	0.25	0.31	0.37	0.44	0.53	0.63	0.73	0.86	1.00	1.19	1.42	1.77	2.52	3.96

	0	50	100	150	200	250	300	350	400	450	500	550	600	650	700	750	800	900
SCPS _b -/ SCPS-/ SCPS _c -/ SCPSi- UHV-HD 07	13.0	10.9	9.3	8.0	6.9	5.9	4.9	4.0	3.1	2.5	1.9	1.4	1.0	0.7	0.5	0.3	0.1	0.1
SCPS _b -/ SCPS-/ SCPS _c -/ SCPSi- UHV-HD 11	27.8	22.2	18.4	16.1	14.7	13.5	12.2	11.2	10.0	8.8	7.5	6.2	4.9	3.7	2.5	1.5	0.7	0.1
SCPS _b -/ SCPS-/ SCPS _c -/ SCPSi- UHV-HD 16	53.2	46.1	40.6	36.1	31.1	25.5	20.4	16.3	13.1	10.9	9.4	8.2	7.0	5.6	3.8	1.6	0.5	0.1

	2.0	2.5	3.0	3.5	4.0	4.5	5.0	5.5	6.0
SCPS _b -/SCPS-/ SCPS _c -/SCPSi-UHV- HD 07	400	511	658	795	896	911	905	899	893
SCPS _b -/SCPS-/ SCPS _c -/SCPSi-UHV- HD 11	421	581	738	867	909	911	909	908	907
SCPS _b -/SCPS-/ SCPS _c -/SCPSi-UHV- HD 16	459	625	786	884	908	912	909	905	901



Art.-Nr.: 10.02.02.07427

**Ordering Data Accessories 10.02.02.07427**

Typ		Item number
Connection cable	ASK B-M12-5 5000 K-5P	21.04.05.00080
Connection cable	ASK B-M12-5 1000 S-M12-5	21.04.05.00158
Connection cable	ASK B-M12-5 2000 S-M12-5	21.04.05.00211
Distributor	ASV SM/CPi B-M12-5 2xS-M12-4	10.02.02.03490
Top-hat rail clamp comp.	HUT-SN-KL 75x18x9 SCPs	10.02.02.04149
Vacuum filter (inline)	VFI CN8/6 50	10.07.01.00245
Vacuum cup filter	VFT G1/4-IG 80	10.07.01.00119

**Ordering Data Spare Parts 10.02.02.07427**

Typ		Item number
Silencer (round)	SD 16.5x51 SCPs	10.02.02.05094
Vacuum set, ejector (inst.)	VACU-SET 16 12.80x76.60 SCPs	10.02.02.05052
Maintenance set ejector	WART SCPs/SCPsi-HD	10.02.02.06343

