Schmalz X-Pump

SCPXi 30 NC Q 2xM12-5

Art.-Nr.: 10.02.02.08183



SCPXi 30 NC Q 2xM12-5


Technical data

Attribute	Value
Electrical connection	2xConnect M12, 2x5 pol
Protection type IP	IP 65 (with plug)
Nozzle size	3.0 mm
Max. vacuum	-850 mbar
Weight	0.850 kg
Air consumption suction	380.0 l/min
Suction rate (max.)	220.0 l/min
Communication	IO-Link (Class A)
Connection	G3/8"-F
Control valve	Normally closed
Operation mode	Pressure Control

The compact ejector SCPXi is delivered as a ready-to-connect product (without a connection cable).

Available spare parts: wear parts kit, silencer, electronics module, pilot valves

Available accessories: connection cable, base plate



Design data SCPXi 30 NC Q 2xM12-5

Design data

Attribute	Value
Length L1	168.00 mm
Width B1	39.00 mm
Height H1	149.50 mm
Height H	137.00 mm
Internal diameter d	5.60 mm
Hole spacing Y1	10.0 mm
Hole spacing X1	89.0 mm
Thread G3	M12x1-M

Contact Schmalz: J. Schmalz GmbH, Johannes-Schmalz-Str. 1 • 72293 Glatten • +49 7443 2403-105 • kundencenter@schmalz.de

Schmalz X-Pump


SCPXi 30 NC Q 2xM12-5

Art.-Nr.: 10.02.02.08183

Technical data

Attribute	Value
Electrical connection	2xConnect M12, 2x5 pol
Protection type IP	IP 65 (with plug)
Nozzle size	3.0 mm
Recommended hose internal diameter compressed air	8.0 mm
Recommended hose internal diameter vacuum	11.0 mm
Degree of evacuation	85.0 %
Max. vacuum	-850 mbar
Weight	850.00 g
Max. air consumption blow-off	320.0 l/min
Air consumption blow-off	19.200 m³/h
Air consumption suction	22.800 m³/h
Suction rate (max.)	13.200 m³/h
Communication	IO-Link (Class A)
Pressure range (operating pressure) [bar]	3.0 ... 6.0 bar
Operating temperature	0 ... 50 °C
Control valve	Normally closed
Operation mode	Pressure Control

Performance data



Achievable vacuum at various operating pressures

Achievable vacuum at various operating pressures

	2	3	4	5	6	7
SCPXi	550.00	780.00	900.00	880.00	860.00	835.00

Contact Schmalz: J. Schmalz GmbH, Johannes-Schmalz-Str. 1 • 72293 Glatten • +49 7443 2403-105 • kundencenter@schmalz.de

Schmalz X-Pump

SCPXi 30 NC Q 2xM12-5

Art.-Nr.: 10.02.02.08183

Further documentation

CAD data and other documents relating to the article can be found at: **www.schmalz.com/10.02.02.08183**

Contact Schmalz: J. Schmalz GmbH, Johannes-Schmalz-Str. 1 • 72293 Glatten • +49 7443 2403-105 • kundencenter@schmalz.de