

RECBi 24V-DC NO PXT-1 1C MATCH


Art.-Nr.: 10.02.03.00397



RECBi 24V-DC NO PXT-1 1C MATCH

The pneumatic vacuum generator RECBi MATCH is available in the following versions:

- With mounted PXR gripper
- With connection flange for modular gripper system PXT
- With mounted universal connection plate



Design data RECBi 24V-DC NO PXT-1 1C MATCH

Technical data

Attribute	Value
Voltage DC	24 V - DC
Additional function area gripper	PXT (1 beam)
Utilization	DIO / IO-Link
Version	Quick-change system MATCH
Control valve	Normally open

Design data

Attribute	Value
Length L2	70.00 mm
Length L	110.50 mm
Width B	75.00 mm
Height H1	74.50 mm
Height H2	25.00 mm
Height H	55.50 mm
Outside diameter D1	86.2 mm
Outside diameter D2	26.5 mm
Outside diameter D	75.50 mm
Height H3	19.00 mm

Art.-Nr.: 10.02.03.00397

**Technical data**

Attribute	Value
Max. vacuum	850 mbar
Voltage DC	24 V - DC
Additional function area gripper	PXT (1 beam)
Rated power	1.51 W
Suction rate (max.)	52.5 l/min
Pressure range (operating pressure) [bar]	3.00 ... 7.00 bar
Operating temperature	0 ... 50 °C
Control valve	Normally open
Voltage	24V - DC
Rated current	0.1 A

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.02.03.00397**Ordering Data Accessories 10.02.03.00397**

Typ		Artikelnummer
Accessories	ZUB RECB-PXT-1 MATCH	10.02.03.00410
Building group Solenoid valve	VENT-BGR EMVP-5 3/2 NC 24V-DC	10.08.09.00032
Storage station	STATION 150x110x22 MATCH	10.08.09.00013
Silencer (cube-shaped-inst.)	SD 66.7x24.4x24.5 RECBi	10.02.03.00441

**Ordering Data Spare Parts 10.02.03.00397**

Typ		Artikelnummer
Set of spare parts	ERS RECB SD	10.02.03.00422
Set of spare parts	ERS SEP-13 6xRUE-KLAP	10.02.01.01449
Ejector module	SEP HV 2 14 13 S	10.02.01.01493
O-ring	O-RING 10.3x2.4 NBR-70	10.07.08.00090

