

Vacuum pump

EVE-TR 25 AC



Art.-Nr.: 10.03.01.00185



EVE-TR 25 AC

The vacuum pump EVE-TR comes ready to connect.


Available spare parts: Filter insert, wearing part set
Available accessories: Vacuum limiter valve

Technical data

Attribute	Value
Rated power at 50 Hz	0.80 kW
Rated power at 60 Hz	1.10 kW
Voltage at 50 Hz	216.2 - 243.8 V
Voltage at 60 Hz	216.2 - 243.8 V
Weight	26.000 kg
Suction rate (50 Hz)	25.000 m ³ /h
Suction rate (60 Hz)	30.000 m ³ /h
Sound pressure level at 50 Hz	62.0 dB(A)
Vacuum (50 Hz)	-850 mbar
Voltage 60 Hz	S047

Design data

Attribute	Value
Length L2	96.00 mm
Length L	505.00 mm
Width B2	40.00 mm
Width B	260.00 mm
Height H	293.00 mm
Internal diameter d	7.00 mm
Thread G3	G3/4-IG
Hole spacing X1	220.0 mm



Design data EVE-TR 25 AC



WWW.SCHMALZ.COM/10.03.01.00185

Vacuum pump

EVE-TR 25 AC



Art.-Nr.: 10.03.01.00185



Technical data

Attribute	Value
Protection type IP	IP 54
Rated power at 50 Hz	0.80 kW
Rated power at 60 Hz	1.10 kW
Voltage at 50 Hz	216.2 - 243.8 V
Voltage at 60 Hz	216.2 - 243.8 V
Weight	26.000 kg
Suction rate (50 Hz)	25.000 m ³ /h
Suction rate (60 Hz)	30.000 m ³ /h
Sound pressure level at 50 Hz	62.0 dB(A)
Product family	EVE-TR
Supply voltage	AC
Current type	A.C. alternating current
Noise level according to DIN EN ISO 3744 (uncertainty factor KpA = 3 dB(A)), interval of 1 m, at medium load, both connection sides piped	



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.03.01.00185



Ordering Data Accessories 10.03.01.00185

Typ		Item number
Vacuum limiter valve	VBV -950...0 G1-AG EVE 10-40	10.03.01.00136
Motor-protection switch	MSS-K 1.6-2.5A	10.04.04.00119
Set of parts subject to wear pump	VST EVE-TR-25	10.03.01.00134
Vacuum reservoir	VOL 50	10.03.03.00118
Silencer box	SBB-EVE-24V-DC-ST-VZ-LUE	10.04.04.00367



Ordering Data Spare Parts 10.03.01.00185

Typ		Item number
Filter insert (round)	FILT-EINS 3 65x70 PAP STF-3/4-IG	10.07.01.00017
Filter insert (round)	FILT-EINS 64x71 PAP EVE-TR-25-40-50	10.03.01.00029



WWW.SCHMALZ.COM/10.03.01.00185