



Art.-Nr.: 10.03.01.00192



EVE-TR-M 2.3 24V-DC

The vacuum pump EVE-TR comes ready to connect.

Available spare parts: Filter insert, wearing part set
Available accessories: Vacuum limiter valve



Design data EVE-TR-M 2.3 24V-DC

Technical data

Attribute	Value
Max. vacuum	-780 mbar
Weight	2.400 kg
Sound pressure level at 50 Hz	72.0 dB(A)

Design data

Attribute	Value
Length L	154.00 mm
Width B2	11.00 mm
Width B	82.00 mm
Height H	123.00 mm
Thread G2	G1/8"-F
Hole spacing Y1	60.0 mm
Hole spacing X1	28.0 mm
Thread G3	G1/8"-F
Thread G5	M4-F




Art.-Nr.: 10.03.01.00192

**Technical data**

Attribute	Value
Max. vacuum	-780 mbar
Weight	2.400 kg
Sound pressure level at 50 Hz	72.0 dB(A)
Suction rate at DC	2.040 m ³ /h
Product family	EVE-TR
Voltage	24V - DC

Noise level according to DIN EN ISO 3744 (uncertainty factor KpA = 3 dB(A)), interval of 1 m, at medium load, both connection sides piped

**Performance data**

Suction rate at various degrees of evacuation

**Suction rate at various degrees of evacuation**

Typ	0	100	200	300	400	500	600	700	780
EVE-TR M 2.3	2.35	2.00	1.68	1.35	1.05	0.77	0.50	0.25	0.05

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.03.01.00192WWW.SCHMALZ.COM/10.03.01.00192