

Art.-Nr.: 10.03.01.00210



EVE-TR-X 10 AC3 F-VB


Vacuum pump EVE-TR-X is delivered as a ready to connect product.

Available spare parts: filter insert, set of parts subject to wear

Available accessories: vacuum regulation valve

Technical data

Attribute	Value
Rated power at 50 Hz	0.37 kW
Rated power at 60 Hz	0.45 kW
Voltage at 50 Hz	175 - 260 / 300 - 450 V AC3
Voltage at 60 Hz	202-300/350-520V AC3
Weight	16.700 kg
Suction rate (50 Hz)	10.000 m ³ /h
Suction rate (60 Hz)	12.000 m ³ /h
Sound pressure level at 50 Hz	60.0 dB(A)
Vacuum (50 Hz)	-850 mbar
Voltage 60 Hz	202-300



Design data EVE-TR-X 10 AC3 F-VB

Design data

Attribute	Value
Length L2	106.00 mm
Length L	429.00 mm
Width B2	60.00 mm
Width B	206.00 mm
Height H1	325.00 mm
Height H2	70.00 mm
Height H	189.00 mm
Internal diameter d	7.00 mm
Thread G2	G3/4"-F
Hole spacing Y1	112.0 mm

Art.-Nr.: 10.03.01.00210

**Technical data**

Attribute	Value
Protection type IP	IP 54
Rated power at 50 Hz	0.37 kW
Rated power at 60 Hz	0.45 kW
Voltage at 50 Hz	175 - 260 / 300 - 450 V AC3
Voltage at 60 Hz	202-300/350-520V AC3
Weight	16.700 kg
Suction rate (50 Hz)	10.000 m ³ /h
Suction rate (60 Hz)	12.000 m ³ /h
Sound pressure level at 50 Hz	60.0 dB(A)
Product family	EVE-TR-X
Supply voltage	AC3
Noise level according to DIN EN ISO 3744 (uncertainty factor KpA = 3 dB(A)), interval of 1 m, at medium load, both connection sides piped	

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.03.01.00210**Ordering Data Wear Parts 10.03.01.00210**

Typ		Item number
Filter insert (round)	FILT-EINS 3 65x70 PAP STF-3/4-IG	10.07.01.00017
Set of parts subject to wear pump	VST EVE-TR-X-10	10.03.01.00223

