


Art.-Nr.: 10.03.01.00270



EVE-TR 360 AC3 IE3-TYP1 F

The vacuum pump EVE-TR comes ready to connect.


Available spare parts: Filter insert, wearing part set
Available accessories: Vacuum limiter valve

Technical data

Attribute	Value
Rated power at 50 Hz	11.00 kW
Rated power at 60 Hz	13.20 kW
Voltage at 50 Hz	D400 V ± 10 %
Voltage at 60 Hz	D460 V ± 10 %
Weight	256.500 kg
Suction rate (50 Hz)	351.000 m ³ /h
Suction rate (60 Hz)	402.000 m ³ /h
Sound pressure level at 50 Hz	80.5 dB(A)
Version	IE3:EU/CN/IND
Vacuum (50 Hz)	-750 mbar
Voltage 60 Hz	S071
Current type	Three phase A.C.
with	Filter

Design data

Attribute	Value
Length L2	124.00 mm
Length L	1,180.00 mm
Width B2	116.00 mm
Width B	644.00 mm
Height H	528.00 mm
Hole spacing Y1	380.0 mm
Hole spacing Y2	190.0 mm
Hole spacing X1	645.0 mm
Thread G3	G2-1/2"-F
Thread G5	M10-F



Design data EVE-TR 360 AC3 IE3-TYP1 F



Art.-Nr.: 10.03.01.00270

**Technical data**

Attribute	Value
Protection type IP	IP 55
Rated power at 50 Hz	11.00 kW
Rated power at 60 Hz	13.20 kW
Voltage at 50 Hz	D400 V ± 10 %
Voltage at 60 Hz	D460 V ± 10 %
Weight	256.500 kg
Suction rate (50 Hz)	351.000 m ³ /h
Suction rate (60 Hz)	402.000 m ³ /h
Sound pressure level at 50 Hz	80.5 dB(A)
Version	IE3:EU/CN/IND
Product family	EVE-TR
Supply voltage	AC3
Current type	Three phase A.C.
Noise level according to DIN EN ISO 3744 (uncertainty factor KpA = 3 dB(A)), interval of 1 m, at medium load, both connection sides piped	

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.03.01.00270

**Ordering Data Spare Parts 10.03.01.00270**

Typ		Item number
Set of parts subject to wear pump	VST EVE-TR-360	10.03.01.00187
Filter insert (round)	FILT-EINS EVE-TR-250/360	10.03.01.00188

