

Art.-Nr.: 10.03.01.00319



EVE-TR 60 AC3 IE3-TYP1

The vacuum pump EVE-TR comes ready to connect.


Available spare parts: Filter insert, wearing part set
Available accessories: Vacuum limiter valve

Technical data

Rated power at 50 Hz	2.20 kW
Rated power at 60 Hz	2.60 kW
Voltage at 50 Hz	D230 V / Y400 V ±10 %
Voltage at 60 Hz	D265 V / Y460 V ±10 %
Weight	76.000 kg
Suction rate (50 Hz)	55.000 m ³ /h
Suction rate (60 Hz)	66.000 m ³ /h
Sound pressure level at 50 Hz	71.0 dB(A)
Version	IE3:EU/CN/IND
Vacuum (50 Hz)	-900 mbar
Voltage 60 Hz	S065
Approval	IE3
Current type	Three phase A.C.

Design data

Length L2	96.00 mm
Length L	704.00 mm
Width B2	46.00 mm
Width B	353.00 mm
Height H	328.00 mm
Internal diameter d	12.00 mm
Hole spacing Y1	190.0 mm
Hole spacing Y2	95.0 mm
Hole spacing X1	326.0 mm
Thread G3	G1"-F
Thread G5	M8-F



Design data EVE-TR 60 AC3 IE3-TYP1

Art.-Nr.: 10.03.01.00319

**Technical data**

Protection type IP	IP 55
Rated power at 50 Hz	2.20 kW
Rated power at 60 Hz	2.60 kW
Voltage at 50 Hz	D230 V / Y400 V ± 10 %
Voltage at 60 Hz	D265 V / Y460 V ± 10 %
Weight	76.000 kg
Suction rate (50 Hz)	55.000 m ³ /h
Suction rate (60 Hz)	66.000 m ³ /h
Sound pressure level at 50 Hz	71.0 dB(A)
Version	IE3:EU/CN/IND
Product family	EVE-TR
Supply voltage	AC3
Current type	Three phase A.C.

Noise level according to DIN EN ISO 3744 (uncertainty factor KpA = 3 dB(A)), interval of 1 m, at medium load, both connection sides piped

**Ordering Data Accessories 10.03.01.00319**

Typ		Item number
Vacuum reservoir	VOL 50	10.03.03.00118

**Ordering Data Wear Parts 10.03.01.00319**

Typ		Item number
Set of parts subject to wear pump	VST EVE-TR60/TR80	22.09.01.00031

