

Art.-Nr.: 10.03.01.00333



Technical data

Rated power at 50 Hz	4.00 kW
Rated power at 60 Hz	4.80 kW
Voltage at 50 Hz	D230 V / Y400 V ±10 %
Voltage at 60 Hz	D265 V / Y460 V ±10 %
Weight	112.000 kg
Suction rate (50 Hz)	129.000 m³/h
Suction rate (60 Hz)	154.000 m³/h
Sound pressure level at 50 Hz	76.0 dB(A)
Voltage at 60 Hz optimal	D230 V / Y400 V ±10 % (without IE3)
Version	IE3:EU/CN/IND
Vacuum (50 Hz)	-900 mbar
Vacuum (60 Hz)	-800 mbar
Voltage 60 Hz	S065
Approval	IE3
Current type	Three phase A.C.
with	Vacuum-limitter valve


EVE-TR-X 140 AC3 IE3-TYP1 VBV

Vacuum pump EVE-TR-X is delivered as a ready to connect product.

Available spare parts: filter insert, set of parts subject to wear

Available accessories: vacuum regulation valve

Design data



Length L2	140.00 mm
Length L	829.00 mm
Width B2	107.50 mm
Width B	470.00 mm
Height H	336.00 mm
Internal diameter d	12.00 mm
Hole spacing Y1	245.0 mm
Hole spacing Y2	122.5 mm
Hole spacing X1	398.0 mm
Thread G3	G1-1/2"-F
Thread G5	M8-F

Design data EVE-TR-X 140 AC3 IE3-TYP1 VBV

Art.-Nr.: 10.03.01.00333

**Technical data**

Protection type IP	IP 55
Rated power at 50 Hz	4.00 kW
Rated power at 60 Hz	4.80 kW
Voltage at 50 Hz	D230 V / Y400 V ±10 %
Voltage at 60 Hz	D265 V / Y460 V ±10 %
Weight	112.000 kg
Suction rate (50 Hz)	129.000 m ³ /h
Suction rate (60 Hz)	154.000 m ³ /h
Sound pressure level at 50 Hz	76.0 dB(A)
Product family	EVE-TR-X
Supply voltage	AC3

Noise level according to DIN EN ISO 3744 (uncertainty factor KpA = 3 dB(A)), interval of 1 m, at medium load, both connection sides piped

**Ordering Data Accessories 10.03.01.00333**

Typ		Item number
Vacuum reservoir	VOL 100	10.03.03.00123

**Ordering Data Spare Parts 10.03.01.00333**

Typ		Item number
Filter insert (round)	FILT-EINS EVE-TR-X-80/100/140	10.03.01.00231
Filter insert (round)	FILT-EINS EVE-TR-X-80	10.03.01.00232

**Ordering Data Wear Parts 10.03.01.00333**

Typ		Item number
Set of parts subject to wear pump	VST EVE-TR-X-140	10.03.01.00234

