


Art.-Nr.: 10.03.01.00340


**Technical data**

Attribute	Value
Rated power at 60 Hz	3.60 kW
Voltage at 60 Hz	YY230 / Y460 V ± 10 %
Weight	109.500 kg
Suction rate (60 Hz)	112.000 m ³ /h
Version	IE3:US/CAN
Voltage 60 Hz	S067
Approval	UL/CSA
Current type	Three phase A.C.
with	Filter

EVE-TR 100 AC3 IE3-TYP2 F

The vacuum pump EVE-TR comes ready to connect.

Available spare parts: Filter insert, wearing part set
 Available accessories: Vacuum limiter valve



Design data EVE-TR 100 AC3 IE3-TYP2 F

Design data

Attribute	Value
Length L1	871.00 mm
Length L2	140.00 mm
Length L	851.00 mm
Width B2	107.50 mm
Width B	470.00 mm
Height H1	426.00 mm
Height H2	75.00 mm
Height H	336.00 mm
Internal diameter d	12.00 mm
Thread G2	G1-1/4"-F




Art.-Nr.: 10.03.01.00340

**Technical data**

Attribute	Value
Protection type IP	IP 55
Rated power at 60 Hz	3.60 kW
Voltage at 60 Hz	YY230 / Y460 V ± 10 %
Weight	109.500 kg
Suction rate (60 Hz)	112.000 m ³ /h
Version	IE3:US/CAN
Product family	EVE-TR
Supply voltage	AC3
Current type	Three phase A.C.

Noise level according to DIN EN ISO 3744 (uncertainty factor KpA = 3 dB(A)), interval of 1 m, at medium load, both connection sides piped

**Performance data**

Suction rate at various degrees of evacuation

**Suction rate at various degrees of evacuation**

TYP	0	200	400	600	800	900
EVE-TR 100 50 Hz	98	77	56	34	12	1
EVE-TR 100 60 Hz	118	90	63	39	17	4

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.03.01.00340

Art.-Nr.: 10.03.01.00340



Ordering Data Accessories 10.03.01.00340

Typ		Item number
Vacuum limiter valve	VBV -950...0 G1-1/4-AG EVE 60-140	10.03.01.00153



Ordering Data Spare Parts 10.03.01.00340

Typ		Item number
Filter insert (round)	FILT-EINS 3 98x70 PAP STF-1-1/4-IGN	10.07.01.00018



Ordering Data Wear Parts 10.03.01.00340

Typ		Item number
Set of parts subject to wear pump	VST EVE-TR-100	22.09.01.00033