


Art.-Nr.: 10.03.01.00348



EVE-TR-X 140 AC3 IE3-TYP2 F-VB

Vacuum pump EVE-TR-X is delivered as a ready to connect product.

Available spare parts: filter insert, set of parts subject to wear


Available accessories: vacuum regulation valve

Technical data

Attribute	Value
Rated power at 60 Hz	4.80 kW
Voltage at 60 Hz	YY230 / Y460 V ± 10 %
Weight	119.500 kg
Suction rate (60 Hz)	154.000 m ³ /h
Voltage at 60 Hz optimal	D208 V ± 10 % (without IE3)
Version	IE3:US/CAN
Vacuum (60 Hz)	-800 mbar
Voltage 60 Hz	S067
Approval	UL/CSA
Current type	Three phase A.C.

Design data

Attribute	Value
Length L1	869.70 mm
Length L2	140.00 mm
Length L	862.00 mm
Width B2	107.50 mm
Width B	470.00 mm
Height H1	425.70 mm
Height H2	75.00 mm
Height H	336.00 mm
Internal diameter d	12.00 mm
Thread G2	G1-1/4"-F



Design data EVE-TR-X 140 AC3 IE3-TYP2 F-VB



Art.-Nr.: 10.03.01.00348

**Technical data**

Attribute	Value
Protection type IP	IP 55
Rated power at 60 Hz	4.80 kW
Voltage at 60 Hz	YY230 / Y460 V ± 10 %
Weight	119.500 kg
Suction rate (60 Hz)	154.000 m ³ /h
Product family	EVE-TR-X
Supply voltage	AC3
Noise level according to DIN EN ISO 3744 (uncertainty factor KpA = 3 dB(A)), interval of 1 m, at medium load, both connection sides piped	

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.03.01.00348**Ordering Data Spare Parts 10.03.01.00348**

Typ		Item number
Filter insert (round)	FILT-EINS EVE-TR-X-80/100/140	10.03.01.00231
Filter insert (round)	FILT-EINS EVE-TR-X-80	10.03.01.00232

**Ordering Data Wear Parts 10.03.01.00348**

Typ		Item number
Set of parts subject to wear pump	VST EVE-TR-X-140	10.03.01.00234

