

Art.-Nr.: 10.03.01.00355



EVE-TR-X 25 AC3 IE3-TYP2 F-VB


Vacuum pump EVE-TR-X is delivered as a ready to connect product.

Available spare parts: filter insert, set of parts subject to wear

Available accessories: vacuum regulation valve

Technical data

Attribute	Value
Rated power at 60 Hz	0.90 kW
Voltage at 60 Hz	YY230 / Y460 V ± 10 %
Weight	28.500 kg
Suction rate (60 Hz)	30.000 m ³ /h
Voltage at 60 Hz optimal	D208 V ± 10 % (without IE3)
Version	IE3:US/CAN
Vacuum (60 Hz)	-900 mbar
Voltage 60 Hz	S067
Approval	UL/CSA
Current type	Three phase A.C.



Design data EVE-TR-X 25 AC3 IE3-TYP2 F-VB

Design data

Attribute	Value
Length L2	96.00 mm
Length L	495.00 mm
Width B2	50.00 mm
Width B	270.00 mm
Height H1	380.00 mm
Height H2	70.00 mm
Height H	292.00 mm
Internal diameter d	7.00 mm
Thread G2	G3/4"-F
Hole spacing Y1	190.0 mm

Art.-Nr.: 10.03.01.00355

**Technical data**

Attribute	Value
Protection type IP	IP 55
Rated power at 60 Hz	0.90 kW
Voltage at 60 Hz	YY230 / Y460 V $\pm 10\%$
Weight	28.500 kg
Suction rate (60 Hz)	30.000 m ³ /h
Product family	EVE-TR-X
Supply voltage	AC3
Noise level according to DIN EN ISO 3744 (uncertainty factor KpA = 3 dB(A)), interval of 1 m, at medium load, both connection sides piped	

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.03.01.00355**Ordering Data Accessories 10.03.01.00355**

Typ	Item number
Silencer box	SBB-EVE-24V-DC-ST-VZ-LUE 10.04.04.00367

**Ordering Data Spare Parts 10.03.01.00355**

Typ	Item number
Set of parts subject to wear pump	VST EVE-TR-X-25 10.03.01.00225
Filter insert (round)	FILT-EINS EVE-TR-X-25/40 10.03.01.00230

**Ordering Data Wear Parts 10.03.01.00355**

Typ	Item number
Set of parts subject to wear pump	VST EVE-TR-X-25 10.03.01.00225

