


Art.-Nr.: 10.03.01.00427



EVE-TR 60 AC3 IE3-TYP3 F


The vacuum pump EVE-TR comes ready to connect.

Available spare parts: Filter insert, wearing part set
Available accessories: Vacuum limiter valve

Technical data

Attribute	Value
Rated power at 50 Hz	2.20 kW
Rated power at 60 Hz	2.60 kW
Voltage at 50 Hz	D200 / Y350 V ± 10 % (without IE3)
Voltage at 60 Hz	D220 V / Y380 - 400 V ± 10 %
Weight	85.500 kg
Suction rate (50 Hz)	55.000 m ³ /h
Suction rate (60 Hz)	66.000 m ³ /h
Sound pressure level at 50 Hz	71.0 dB(A)
Version	IE3:JPN/KOR/BRA
Vacuum (50 Hz)	-900 mbar

Design data



Attribute	Value
Length L1	768.70 mm
Length L2	96.00 mm
Length L	747.00 mm
Width B2	46.00 mm
Width B	353.00 mm
Height H1	414.40 mm
Height H2	75.00 mm
Height H	328.00 mm
Internal diameter d	12.00 mm
Thread G2	G1-1/4"-F

Design data EVE-TR 60 AC3 IE3-TYP3 F



Art.-Nr.: 10.03.01.00427

**Technical data**

Attribute	Value
Protection type IP	IP 55
Rated power at 50 Hz	2.20 kW
Rated power at 60 Hz	2.60 kW
Voltage at 50 Hz	D200 / Y350 V ± 10 % (without IE3)
Voltage at 60 Hz	D220 V / Y380 - 400 V ± 10 %
Weight	85.500 kg
Suction rate (50 Hz)	55.000 m ³ /h
Suction rate (60 Hz)	66.000 m ³ /h
Sound pressure level at 50 Hz	71.0 dB(A)
Version	IE3:JPN/KOR/BRA
Product family	EVE-TR
Supply voltage	AC3
Current type	Three phase A.C.
Noise level according to DIN EN ISO 3744 (uncertainty factor KpA = 3 dB(A)), interval of 1 m, at medium load, both connection sides piped	

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.03.01.00427**Ordering Data Accessories 10.03.01.00427**

Typ	Item number
Vacuum limiter valve	VBV -950...0 G1-1/4-AG EVE 60-140
	10.03.01.00153

**Ordering Data Spare Parts 10.03.01.00427**

Typ	Item number
Filter insert (round)	FILT-EINS 3 98x70 PAP STF-1-1/4-IGN
	10.07.01.00018
Set of parts subject to wear pump	VST EVE-TR60/TR80
	22.09.01.00031

