


Art.-Nr.: 10.03.01.00500



ECBPMi 24V-DC FK

Technical data

Attribute	Value
Electrical connection	Spring contact
Voltage DC	24 V - DC
Suction rate (max.)	1.6 l/min
Rated power	7.20 W
Operating temperature	0 ... 40 °C
Rated current	0.3 A



Design data ECBPMi 24V-DC FK

Design data

Attribute	Value
Length L1	61.40 mm
Length L	56.40 mm
Outside diameter D2	35.5 mm
Outside diameter D	63.00 mm
Thread G1	M4-F
Thread length LG1	6.0 mm
Thread G2	G1/4"-F
Thread length LG2	11.0 mm
Pitch diameter D mk1	46.0 mm

Art.-Nr.: 10.03.01.00500

**Technical data**

Attribute	Value
Electrical connection	Spring contact
Voltage DC	24 V - DC
Suction rate (max.)	1.6 l/min
Rated power	7.20 W
Operating temperature	0 ... 40 °C
Rated current	0.3 A

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.03.01.00500

**Ordering Data Spare Parts 10.03.01.00500**

Typ	Item number
Bellows suction cups (round)	SPB1 30 ED-65 G1/8-AG 10.01.06.03496

