


Art.-Nr.: 10.03.01.00556



ECBPMi 24V-DC M12-8

The ECBPMi electric vacuum generator is supplied as a ready-to-connect product.



Design data ECBPMi 24V-DC M12-8

Technical data

Attribute	Value
Electrical connection	Male connect M12, 8 pol
Voltage DC	24 V - DC
Operating temperature	0 ... 40 °C
Rated current	0.3 A

Design data

Attribute	Value
Length L1	73.40 mm
Length L	67.40 mm
Outside diameter D2	31.5 mm
Outside diameter D	63.00 mm
Internal diameter d	7.00 mm
Thread G1	M4-F
Thread length LG1	6.0 mm
Thread G2	G1/4"-F
Thread length LG2	11.0 mm
Cable length	475.50 mm

Art.-Nr.: 10.03.01.00556

**Technical data**

Attribute	Value
Electrical connection	Male connect M12, 8 pol
Protection type IP	IP 40
Voltage DC	24 V - DC
Operating temperature	0 ... 40 °C
Product family	ECBPMi
Rated current	0.3 A
contains	Screws

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.03.01.00556

**Ordering Data Accessories 10.03.01.00556**

Typ		Item number
Flange plate (round)	FLAN-PL 63x14-ROH ECBPM	10.03.01.00535
Lightweight Gripper	SLG 102x57 FSGA 2	10.01.10.14043
Lightweight Gripper	SLG 102x102 FSGA 3	10.01.10.14042
Lightweight Gripper	SLG 102x75.3 FSGA 4	10.01.10.14041
Flange extension VEE-FE	VEE-FE 25.4x81.5	10.01.36.00130
Flange extension VEE-FE	VEE-FE 25.4x131.5	10.01.36.00109
Flange extension VEE-FE	VEE-FE 25.4x181.5	10.01.36.00128

**Ordering Data Spare Parts 10.03.01.00556**

Typ		Item number
CobotPump	ECBPMi 24V-DC FK	10.03.01.00500
Bellows suction cups (round)	SPB1 30 ED-65 G1/4-AG	10.01.06.04530
Flat suction pad (round)	SFF 20 SI-55 G1/4-AG	10.01.01.14621

