

Art.-Nr.: 10.03.01.00626



Technical data


Attribute	Value
Max. vacuum	750 mbar
Suction rate (max.)	12.0 l/min
Rated power	13.00 W
Operating temperature	5 ... 45 °C
Version	Quick-change system MATCH
Voltage	24V - DC
Rated current	0.6 A

ECBPi 12 24V-DC MATCH

The delivery consists of:

- Electrical vacuum generator ECBPi MATCH
- Suction cup SFF / SPB1
- USB stick with software
- G1/4" -F flange for suction cup connection

Suitable quick-change module RMQC must be ordered separately.



Design data ECBPi 12 24V-DC MATCH

Design data

Attribute	Value
Length L1	155.50 mm
Length L2	114.00 mm
Length L	143.00 mm
Outside diameter D1	86.5 mm
Outside diameter D	151.50 mm
Length L3	18.00 mm
Hole spacing X1	43.0 mm



Art.-Nr.: 10.03.01.00626

**Technical data**

Attribute	Value
Max. vacuum	750 mbar
Weight	1,135.0 g
Voltage DC	24 V - DC
Suction rate (max.)	12.0 l/min
Rated power	13.00 W
Operating temperature	5 ... 45 °C
Rated current	0.6 A

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.03.01.00626**Ordering Data Accessories 10.03.01.00626**

Typ		Artikelnummer
Storage station	STATION 150x110x22 MATCH	10.08.09.00013
Flange set robots	SET PXT 46 1LT ECBPi	10.01.49.00085
Quick change module RMQC	RMQC 50 URe DIO WB-M8-8 NPN MATCH	10.08.09.00001
Quick change module RMQC	RMQC 50 HANWHA DIO WB-M8-8 NPN MATCH	10.08.09.00002
Quick change module RMQC	RMQC 50 DOOSAN DIO WS-M8-8 PNP MATCH	10.08.09.00003
Quick change module RMQC	RMQC 50 TM DIO WS-M8-8 NPN MATCH	10.08.09.00004
Quick change module RMQC	RMQC 50 FANUC DIO WB-M8-8 PNP MATCH	10.08.09.00005
Quick change module RMQC	RMQC 50 URe RS-485 WB-M8-8 MATCH	10.08.09.00010
Quick change module RMQC	RMQC 50 ABB DIO 2xM8-3/4 PNP MATCH	10.08.09.00016
Quick change module RMQC	RMQC 50 ABB IOL 2xM8-3/4 MATCH	10.08.09.00017
Quick change module RMQC	RMQC 50 ABB IOL LED 2xM8-3/4 MATCH	10.08.09.00018
Quick change module RMQC	RMQC 31.5 ABB IOL M12-12 MATCH	10.08.09.00019
Quick change module RMQC	RMQC 31.5 ABB IOL LED M12-12 MATCH	10.08.09.00020
Quick change module RMQC	RMQC 31.5 ABB DIO M12-12 PNP MATCH	10.08.09.00021
Quick change module RMQC	RMQC 31.5 ABB IOL M12-12 MATCH	10.08.09.00022
Quick change module RMQC	RMQC 31.5 ABB IOL LED M12-12 MATCH	10.08.09.00023
Suction cup	RFBP 50 50 BA SPB2	10.01.45.00096
Suction cup	RFBP 100 58 BA SPB2	10.01.45.00091
Suction cup	RFBP 100 58 BA O10	10.01.45.00092
Suction cup	RFBP 120 120 BA SPB2	10.01.45.00085
Suction cup	RFBP 120 120 BA O10	10.01.45.00086
Flange extension VEE-FE	VEE-FE 25.4x81.5	10.01.36.00130
Flange extension VEE-FE	VEE-FE 25.4x131.5	10.01.36.00109
Flange extension VEE-FE	VEE-FE 25.4x181.5	10.01.36.00128

