

Art.-Nr.: 10.03.01.00661




ECBPMi 24V-DC MATCH

The delivery consists of:

- Electrical vacuum generator ECBPMi MATCH
- Suction cup SFF / SPB1
- USB stick with software

Suitable quick-change module RMQC must be ordered separately.



Design data ECBPMi 24V-DC MATCH

Technical data

Attribute	Value
Suction rate (max.)	1.6 l/min
Rated power	7.20 W
Operating temperature	0 ... 40 °C
Version	Quick-change system MATCH
Voltage	24V - DC
Rated current	0.3 A

Design data

Attribute	Value
Length L1	123.90 mm
Length L2	81.90 mm
Length L	110.90 mm
Outside diameter D1	86.5 mm
Outside diameter D	75.00 mm
Thread length LG1	6.0 mm
Thread G2	G1/4"-F
Thread length LG2	11.0 mm
Length L3	18.10 mm
Hole spacing X1	43.0 mm



Art.-Nr.: 10.03.01.00661

**Technical data**

Attribute	Value
Degree of evacuation	60.0 %
Voltage DC	24 V - DC
Suction rate (max.)	1.6 l/min
Rated power	7.20 W
Operating temperature	0 ... 40 °C
Rated current	0.3 A
Lift capacity (vertical)	30.0 N
Lift capacity (horizontal)	10.0 N

**Further documentation**

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.03.01.00661

**Ordering Data Accessories 10.03.01.00661**

Typ		Artikelnummer
Storage station	STATION 150x110x22 MATCH	10.08.09.00013
Quick change module RMQC	RMQC 50 URe DIO WB-M8-8 NPN MATCH	10.08.09.00001
Quick change module RMQC	RMQC 50 HANWHA DIO WB-M8-8 NPN MATCH	10.08.09.00002
Quick change module RMQC	RMQC 50 DOOSAN DIO WS-M8-8 PNP MATCH	10.08.09.00003
Quick change module RMQC	RMQC 50 TM DIO WS-M8-8 NPN MATCH	10.08.09.00004
Quick change module RMQC	RMQC 50 FANUC DIO WB-M8-8 PNP MATCH	10.08.09.00005
Quick change module RMQC	RMQC 50 URe RS-485 WB-M8-8 MATCH	10.08.09.00010
Quick change module RMQC	RMQC 50 ABB DIO 2xM8-3/4 PNP MATCH	10.08.09.00016
Quick change module RMQC	RMQC 50 ABB IOL 2xM8-3/4 MATCH	10.08.09.00017
Quick change module RMQC	RMQC 50 ABB IOL LED 2xM8-3/4 MATCH	10.08.09.00018
Quick change module RMQC	RMQC 31.5 ABB IOL M12-12 MATCH	10.08.09.00019
Quick change module RMQC	RMQC 31.5 ABB IOL LED M12-12 MATCH	10.08.09.00020
Quick change module RMQC	RMQC 31.5 ABB DIO M12-12 PNP MATCH	10.08.09.00021
Quick change module RMQC	RMQC 31.5 ABB IOL M12-12 MATCH	10.08.09.00022
Quick change module RMQC	RMQC 31.5 ABB IOL LED M12-12 MATCH	10.08.09.00023
Lightweight Gripper	SLG 102x57 FSGA 2	10.01.10.14043
Lightweight Gripper	SLG 102x102 FSGA 3	10.01.10.14042
Lightweight Gripper	SLG 102x75.3 FSGA 4	10.01.10.14041
Flange extension VEE-FE	VEE-FE 25.4x81.5	10.01.36.00130
Flange extension VEE-FE	VEE-FE 25.4x131.5	10.01.36.00109
Flange extension VEE-FE	VEE-FE 25.4x181.5	10.01.36.00128

