


Art.-Nr.: 10.03.01.00689




EVE-KL 150 AC3 IE3-TYP3 F

The claw pump EVE-KL, available in three sizes for all common supply voltages, is supplied as a ready-to-connect product.

Available spare parts: Replacement filters in paper and polyester

## Technical data

| Attribute            | Value                      |
|----------------------|----------------------------|
| Rated power at 50 Hz | 3.00 kW                    |
| Rated power at 60 Hz | 3.60 kW                    |
| Voltage 50 Hz        | S081                       |
| Voltage at 50 Hz     | D200 V / Y350 V $\pm 10$ % |
| Weight               | 200.000 kg                 |
| Suction rate (50 Hz) | 150.000 m <sup>3</sup> /h  |
| Suction rate (60 Hz) | 180.000 m <sup>3</sup> /h  |
| Version              | IE3:JPN/KOR/BRA            |
| Vacuum (50 Hz)       | 900 mbar                   |
| Vacuum (60 Hz)       | 900 mbar                   |



Design data EVE-KL 150 AC3 IE3-TYP3 F

## Design data

| Attribute       | Value     |
|-----------------|-----------|
| Length L1       | 847.00 mm |
| Length L2       | 70.00 mm  |
| Length L        | 735.00 mm |
| Width B1        | 537.00 mm |
| Width B2        | 70.00 mm  |
| Width B         | 440.00 mm |
| Height H1       | 579.50 mm |
| Height H        | 478.00 mm |
| Thread G2       | G1-1/2"-F |
| Hole spacing Y1 | 300.0 mm  |

Art.-Nr.: 10.03.01.00689

**Technical data**

| Attribute            | Value                      |
|----------------------|----------------------------|
| Protection type IP   | IP 55                      |
| Rated power at 50 Hz | 3.00 kW                    |
| Rated power at 60 Hz | 3.60 kW                    |
| Voltage at 50 Hz     | D200 V / Y350 V $\pm 10$ % |
| Weight               | 200.000 kg                 |
| Suction rate (50 Hz) | 150.000 m <sup>3</sup> /h  |
| Suction rate (60 Hz) | 180.000 m <sup>3</sup> /h  |
| Version              | IE3:JPN/KOR/BRA            |
| Vacuum (50 Hz)       | 900 mbar                   |
| Vacuum (60 Hz)       | 900 mbar                   |
| Supply voltage       | AC3                        |
| Current type         | Three phase A.C.           |

**Further documentation**CAD data and other documents relating to the article can be found at: [www.schmalz.com/10.03.01.00689](http://www.schmalz.com/10.03.01.00689)**Ordering Data Spare Parts 10.03.01.00689**

| Typ                   |                              | Item number    |
|-----------------------|------------------------------|----------------|
| Filter insert (round) | FILT-EINS 197x102 PAP EVE-KL | 10.03.01.00701 |
| Filter insert (round) | FILT-EINS 197x102 PES EVE-KL | 10.03.01.00702 |
| Oil                   | OEL EVE-KL 1L                | 27.02.01.00078 |

