

Art.-Nr.: 10.03.01.00692



EVE-KL 300 AC3 IE3-TYP2 F


The claw pump EVE-KL, available in three sizes for all common supply voltages, is supplied as a ready-to-connect product.

Available spare parts: Replacement filters in paper and polyester

Technical data

Attribute	Value
Rated power at 50 Hz	7.50 kW
Rated power at 60 Hz	7.50 kW
Voltage 50 Hz	S064
Voltage at 50 Hz	D230 V / Y400 V ± 10 %
Weight	328.000 kg
Suction rate (50 Hz)	275.000 m ³ /h
Suction rate (60 Hz)	325.000 m ³ /h
Version	IE3:US/CAN
Vacuum (50 Hz)	850 mbar
Vacuum (60 Hz)	850 mbar
Voltage 60 Hz	S097
Approval	UL/CSA
with	Filter

Design data



Design data EVE-KL 300 AC3 IE3-TYP2 F

Attribute	Value
Length L1	918.00 mm
Length L2	71.00 mm
Length L	808.00 mm
Width B1	580.00 mm
Width B2	91.50 mm
Width B	483.00 mm
Height H1	624.00 mm
Height H	541.00 mm
Thread G2	G2"-F
Hole spacing Y1	300.0 mm
Hole spacing X1	670.0 mm
Thread G3	G2-1/2"-F
Thread G5	M10-F

Art.-Nr.: 10.03.01.00692

**Technical data**

Attribute	Value
Protection type IP	IP 55
Rated power at 50 Hz	7.50 kW
Rated power at 60 Hz	7.50 kW
Voltage at 50 Hz	D230 V / Y400 V ± 10 %
Weight	328.000 kg
Suction rate (50 Hz)	275.000 m ³ /h
Suction rate (60 Hz)	325.000 m ³ /h
Version	IE3:US/CAN
Vacuum (50 Hz)	850 mbar
Vacuum (60 Hz)	850 mbar
Supply voltage	AC3
Current type	Three phase A.C.

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.03.01.00692**Ordering Data Spare Parts 10.03.01.00692**

Typ		Item number
Filter insert (round)	FILT-EINS 197x102 PAP EVE-KL	10.03.01.00701
Filter insert (round)	FILT-EINS 197x102 PES EVE-KL	10.03.01.00702
Oil	OEL EVE-KL 1L	27.02.01.00078

