

Art.-Nr.: 10.03.01.00693




EVE-KL 300 AC3 IE3-TYP3 F

The claw pump EVE-KL, available in three sizes for all common supply voltages, is supplied as a ready-to-connect product.

Available spare parts: Replacement filters in paper and polyester

Technical data

Rated power at 50 Hz	5.50 kW
Rated power at 60 Hz	6.60 kW
Voltage 50 Hz	S081
Voltage at 50 Hz	D200 V / Y350 V $\pm 10\%$
Weight	331.000 kg
Suction rate (50 Hz)	275.000 m ³ /h
Suction rate (60 Hz)	325.000 m ³ /h
Version	IE3:JPN/KOR/BRA
Vacuum (50 Hz)	850 mbar
Vacuum (60 Hz)	850 mbar
Voltage 60 Hz	S094
Approval	UL/CSA
with	Filter



Design data EVE-KL 300 AC3 IE3-TYP3 F

Design data

Length L1	918.00 mm
Length L2	71.00 mm
Length L	808.00 mm
Width B1	580.00 mm
Width B2	91.50 mm
Width B	483.00 mm
Height H1	624.00 mm
Height H	541.00 mm
Thread G2	G2"-F
Hole spacing Y1	300.0 mm
Hole spacing X1	670.0 mm
Thread G3	G2-1/2"-F
Thread G5	M10-F

Art.-Nr.: 10.03.01.00693



Technical data

Protection type IP	IP 55
Rated power at 50 Hz	5.50 kW
Rated power at 60 Hz	6.60 kW
Voltage at 50 Hz	D200 V / Y350 V ±10 %
Weight	331.000 kg
Suction rate (50 Hz)	275.000 m ³ /h
Suction rate (60 Hz)	325.000 m ³ /h
Version	IE3:JPN/KOR/BRA
Vacuum (50 Hz)	850 mbar
Vacuum (60 Hz)	850 mbar
Supply voltage	AC3
Current type	Three phase A.C.



Ordering Data Spare Parts 10.03.01.00693

Typ		Item number
Filter insert (round)	FILT-EINS 197x102 PAP EVE-KL	10.03.01.00701
Filter insert (round)	FILT-EINS 197x102 PES EVE-KL	10.03.01.00702
Oil	OEL EVE-KL 1L	27.02.01.00078

