


Art.-Nr.: 10.03.01.00813




EVE-TR 4 AC3 IE2-TYP1 F

The vacuum pump EVE-TR comes ready to connect.

Available spare parts: Filter insert, wearing part set
Available accessories: Vacuum limiter valve

Technical data

Rated power at 50 Hz	0.18 kW
Rated power at 60 Hz	0.22 kW
Voltage at 50 Hz	230 / 400 V AC3
Voltage at 60 Hz	208 / 360 V AC3
Weight	7.270 kg
Suction rate (50 Hz)	4.100 m ³ /h
Suction rate (60 Hz)	4.700 m ³ /h
Sound pressure level at 50 Hz	59.0 dB(A)
Vacuum (50 Hz)	-850 mbar
Voltage 60 Hz	208/360AC3
Current type	Three phase A.C.
with	Filter



Design data EVE-TR 4 AC3 IE2-TYP1 F

Design data

Length L1	267.00 mm
Length L2	72.00 mm
Length L	221.50 mm
Width B2	11.50 mm
Width B	155.00 mm
Height H1	167.00 mm
Height H2	25.00 mm
Height H	148.00 mm
Internal diameter d	7.00 mm
Thread G2	G1/4"-F
Hole spacing Y1	100.0 mm
Hole spacing X1	80.0 mm
Thread G3	G1/4"-F

Art.-Nr.: 10.03.01.00813

**Technical data**

Protection type IP	IP 54
Rated power at 50 Hz	0.18 kW
Rated power at 60 Hz	0.22 kW
Voltage at 50 Hz	230 / 400 V AC3
Voltage at 60 Hz	208 / 360 V AC3
Weight	7.270 kg
Suction rate (50 Hz)	4.100 m ³ /h
Suction rate (60 Hz)	4.700 m ³ /h
Sound pressure level at 50 Hz	59.0 dB(A)
Product family	EVE-TR
Supply voltage	AC3
Current type	Three phase A.C.

Noise level according to DIN EN ISO 3744 (uncertainty factor KpA = 3 dB(A)), interval of 1 m, at medium load, both connection sides piped

**Ordering Data Accessories 10.03.01.00813**

Typ		Item number
Vacuum limiter valve	VBV -850...0 G3/8-AG EVE 4-8	10.03.01.00107

**Ordering Data Spare Parts 10.03.01.00813**

Typ		Item number
Filter insert (round)	FILT-EINS 15 27x23 A2 VF-1/4-Draht	10.07.01.00013
Set of parts subject to wear pump	VST EVE-TR-4	10.03.01.00108

