

Art.-Nr.: 10.03.01.00833




EVE-KL 150 AC3 FU

The claw pump EVE-KL, available in three sizes for all common supply voltages, is supplied as a ready-to-connect product.

Available spare parts: Replacement filters in paper and polyester

Technical data

Attribute	Value
Rated power at 60 Hz	4.00 kW
Voltage at 50 Hz	400 - 480 V AC3
Weight	208.000 kg
Suction rate (60 Hz)	180.000 m ³ /h
Vacuum (60 Hz)	900 mbar
Voltage 60 Hz	400-480AC3
Approval	UL/CSA
with	Frequency converter control



Design data EVE-KL 150 AC3 FU

Design data

Attribute	Value
Length L1	833.00 mm
Length L2	70.00 mm
Length L	735.00 mm
Width B1	537.00 mm
Width B2	70.00 mm
Width B	440.00 mm
Height H1	579.50 mm
Height H	478.00 mm
Thread G2	G1-1/2"-F
Hole spacing Y1	300.0 mm

Art.-Nr.: 10.03.01.00833

**Technical data**

Attribute	Value
Protection type IP	IP 55
Rated power at 60 Hz	4.00 kW
Voltage at 50 Hz	400 - 480 V AC3
Voltage at 60 Hz	400 - 480 V AC3
Weight	208.000 kg
Suction rate (60 Hz)	180.000 m ³ /h
Vacuum (60 Hz)	900 mbar
Supply voltage	AC3
Current type	Three phase A.C.

**Further documentation**CAD data and other documents relating to the article can be found at: www.schmalz.com/10.03.01.00833**Ordering Data Spare Parts 10.03.01.00833**

Typ		Item number
Filter insert (round)	FILT-EINS 197x102 PAP EVE-KL	10.03.01.00701
Filter insert (round)	FILT-EINS 197x102 PES EVE-KL	10.03.01.00702
Oil	OEL EVE-KL 1L	27.02.01.00078

