

# VZ-OG 165 AC3 200 GMS

Art.-Nr.: 10.03.04.00165



## Technical data


Reservoir volume	200.0 l
Suction rate -800	165.0 m <sup>3</sup> /h
Voltage	230/400V ±10%
with	regulated engine circuit

VZ-OG 165 AC3 200 GMS

Vacuum centre VZ is delivered as a ready to connect product.

Available spare parts: replacement cartridge for air cleaner, replacement cartridge for oil filter

Available accessories: filter cartridge for vacuum reservoir



## Design data

Length L1	1,040.00 mm
Length L	910.00 mm
Width B1	1,040.00 mm
Width B	710.00 mm
Height H	950.00 mm
Internal diameter d	11.00 mm
Thread G2	G2-1/2"-F
Hole spacing Y1	670.0 mm
Hole spacing X1	592.0 mm

Design data VZ-OG 165 AC3 200 GMS



# VZ-OG 165 AC3 200 GMS



Art.-Nr.: 10.03.04.00165

## Technical data

Protection type IP	IP 44
Max. vacuum	-750 mbar
Motor power	4.00 kW
Weight	273.000 kg
Reservoir volume	200.0 l
Suction rate -800	165.0 m <sup>3</sup> /h
Product family	VZ
Voltage	230/400V ±10%

## Ordering Data Accessories 10.03.04.00165

Typ		Item number
Oil	OEL EVE-OG 1L ANDEROL 555	27.02.01.00055
Oil	OEL EVE-OG 5L ANDEROL 555	27.02.01.00056

## Ordering Data Spare Parts 10.03.04.00165

Typ		Item number
Filter insert (round)	FILT-EINS 3 150x222 PAP STF-2-1/2-IG	10.07.01.00020
Oil filter	OEL-FILT EVE-OG-250	10.03.02.00011

## Ordering Data Wear Parts 10.03.04.00165

Typ		Item number
Set of parts subject to wear pump	VST EVE-OG-165-255	10.03.02.00057