




EVE-WR 25 AC3

Vakum pompası EVE-WR bağlanmaya hazır bir ürün olarak teslim edilir.

Mevcut aksesuarlar: ek filtre, motor koruma şalteri

Teknik veriler

Attribute	Value
Nominal güç 50 Hz	0.83 kW
Nominal güç 60 Hz	0.83 kW
50 Hz'de Gerilim	200 - 240 V veya 345 - 420 V
Ağırlık	38.000 kg
Vakum debisi (50 Hz)	25.000 m ³ /h
50 Hz'de ses seviyesi	63.0 dB(A)
Mevcut tip	üç fazlı akım



Tasarım verileri EVE-WR 25 AC3

Tasarım verileri

Attribute	Value
Uzunluk L2	85.00 mm
Uzunluk L	602.00 mm
Genişlik B	432.00 mm
Yükseklik H1	486.00 mm
Yükseklik H	390.00 mm
Dış çap D2	30.0 mm
İç çap d	14.00 mm
Delik aralığı Y1	370.0 mm
Delik aralığı X1	345.0 mm

Vakum pompası
EVE-WR 25 AC3



Art.-Nr.: 10.03.05.00014



Teknik veriler

Attribute	Value
Koruma tipi IP	IP 54
Nominal güç 50 Hz	0.83 kW
Nominal güç 60 Hz	0.83 kW
50 Hz'de Gerilim	200 - 240 V veya 345 - 420 V
60 Hz'de Gerilim	200 - 275 V veya 345 - 480 V
Ağırlık	38.000 kg
Vakum debisi (50 Hz)	25.000 m³/h
50 Hz'de ses seviyesi	63.0 dB(A)
Mevcut tip	AC3



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.03.05.00014



Discontinued item

The product family will be discontinued and is available until **31.12.2025**
Starting from this time, the article can no longer be ordered.
alternative article



Veri aksesuarları sipariş edin 10.03.05.00014

Typ	Ürün numarası
Motor koruma şalteri	MSS-K 2.5-4A
	10.04.04.00120



WWW.SCHMALZ.COM/10.03.05.00014