

Art.-Nr.: 10.04.01.00067



SB 130 125 0.75 IE3-TYP3

The vacuum blower SB is delivered as a ready-to-connect product.


Available accessories: silencer box, dust filter

Technical data

Attribute	Value
Rated power at 50 Hz	0.75 kW
Rated power at 60 Hz	0.90 kW
Voltage at 50 Hz	D200 V / Y350 V ± 10 %
Voltage at 60 Hz	D220 V / Y380 - 400 V ± 10 %
Weight	21.700 kg
Suction rate (50 Hz)	130.000 m ³ /h
Suction rate (60 Hz)	160.000 m ³ /h
Color	RAL 7035 Light grey
Version	IE3:JPN/KOR/BRA
Vacuum (50 Hz)	125 mbar

Design data

Attribute	Value
Length L	387.00 mm
Width B1	295.00 mm
Width B	264.00 mm
Height H	309.00 mm
Outside diameter D2	40.0 mm
Internal diameter d	10.20 mm
Thread G1	G1-1/2"-F
Hole spacing Y1	240.0 mm
Hole spacing X1	240.0 mm



Design data SB 130 125 0.75 IE3-TYP3




Art.-Nr.: 10.04.01.00067

**Technical data**

Attribute	Value
Protection type IP	IP 55
Rated power at 50 Hz	0.75 kW
Rated power at 60 Hz	0.90 kW
Voltage at 50 Hz	D200 V / Y350 V ± 10 %
Voltage at 60 Hz	D220 V / Y380 - 400 V ± 10 %
Weight	21.700 kg
Suction rate (50 Hz)	130.000 m ³ /h
Suction rate (60 Hz)	160.000 m ³ /h
Sound pressure level at 50 Hz	56.8 dB(A)
Version	IE3:JPN/KOR/BRA
Vacuum (50 Hz)	125 mbar
Vacuum (60 Hz)	115 mbar
Product family	SB
Version design	IE3-TYP3
Sound pressure level at 60 Hz	61.7 dB(A)

Noise level according to DIN EN ISO 3744 (uncertainty factor KpA = 3 dB(A)), interval of 1 m, at medium load, both connection sides piped

**Performance data**

Suction rate at various degrees of evacuation

**Suction rate at various degrees of evacuation**

	0	40	80	120
SB-130-125 (50 Hz)	130	117	107	93
SB-160-115 (60 Hz)	163	150	137	122



Vacuum blower

SB 130 125 0.75 IE3-TYP3



Art.-Nr.: 10.04.01.00067



Further documentation

CAD data and other documents relating to the article can be found at: www.schmalz.com/10.04.01.00067



Ordering Data Accessories 10.04.01.00067

Typ		Item number
Dust filter	STF 40 P 4.5 SSD	10.07.01.00398
Silencer (round)	SD G1-1/2-AG 113x410 SB	10.04.04.00362



WWW.SCHMALZ.COM/10.04.01.00067